


O5P700



Retro-reflective laser sensor

O5PLFPKG/US100



- 1 programming buttons
2 When a M5 mounting screw is used, the max. tightening torque is 2 Nm.



Product characteristics

Type of light	red light
Laser protection class	1
Housing	rectangular

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	655

Outputs

Electrical design	PNP
Output function	light-on/dark-on mode; (programmable)

O5P700



Retro-reflective laser sensor

O5PLFPKG/US100

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	2000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range referred to prismatic reflector	[m]	15; (Prismatic reflector Ø 80 E20005)
Range adjustable		yes
Diameter of the smallest detectable object	[mm]	3; (1 m; 15 m: 20)
Max. light spot diameter	[mm]	40
Light spot dimensions refer to		at maximum range
Polarisation filter available		yes

Operating conditions

Ambient temperature	[°C]	-10...60
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
Laser protection class		1
Notes on laser protection	Caution:	laser light
	laser class:	1
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF	[ANN]	602

Mechanical data

Weight	[g]	71
Housing		rectangular
Dimensions	[mm]	56 x 18.2 x 46.8
Materials		housing: PA; bezel: stainless steel; operator interface: TPU
Lens material		PMMA
Lens alignment		side lens

Displays / operating elements

Display	switching status	1 x LED, yellow
Teach function		yes
Electronic lock		yes

Remarks

Remarks	operating voltage "supply class 2" according to cULus	
Pack quantity	1 pcs.	

O5P700



Retro-reflective laser sensor

O5PLFPKG/US100

Electrical connection

Connector: 1 x M12; coding: A



Connection

