


Capacitive sensor

KNM18NUKFPKG/PP/US

Article no longer available - archive entry

Alternative articles: KG5071

When selecting an alternative article and accessories please note that technical data may differ!



1 programming button



Product characteristics

Electrical design	PNP
Output function	normally open / normally closed; (selectable)
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 84

Application

Special feature	Gold-plated contacts
Media	powder; liquids; oils; coolants

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	17; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	5
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

KN5113



Capacitive sensor

KNM18NUKFPKG/PP/US

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1 / L = 84
Thread designation		M18 x 1
Materials		PP

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Аксессуары

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated

