


KQ6016



Capacitive sensor

KQ-3120NFNKG/2T/2M/US



- 1 Sensing face
- 2 programming buttons
- 3 LED



Product characteristics

Electrical design	NPN
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	12
Communication interface	IO-Link
Housing	rectangular
Dimensions [mm]	20 x 14 x 48

Application

Installation	detection through non-metallic container wall or on bypass pipes
Media	dry bulk material; liquids

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 17
Protection class	III
Reverse polarity protection	yes
Measuring principle	capacitive

Outputs

Electrical design	NPN
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	10
Short-circuit protection	yes

KQ6016



Capacitive sensor

KQ-3120NFKG/2T/2M/US

Overload protection	yes	
Detection zone		
Sensing range	[mm]	12
Real sensing range Sr	[mm]	12 ± 10 %
Accuracy / deviations		
Hysteresis	[X01]	1...15
Switch point drift	[X01]	-20...20
Interfaces		
Communication interface	IO-Link	
Transmission type	COM1 (4,8 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor	
SIO mode	yes	
Min. process cycle time	[ms]	100.8
Supported DeviceIDs	Type of operation	DeviceID
	default	371
Operating conditions		
Ambient temperature	[°C]	-25...80
Note on ambient temperature	for UL application: ...50 °C	
Protection	IP 65; IP 67; IP 69K	
Tests / approvals		
EMC	EN 61000-4-2 ESD	30 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
Shock resistance	EN 60068-2-27	30 g 6 shocks / 11 ms half-sine (x, y, z)
Vibration resistance	EN 60068-2-6	(10...55 Hz) / 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
MTTF	[ANN]	634
UL approval	Ta	-25...50 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
Mechanical data		
Weight	[g]	57.5
Housing	rectangular	
Mounting	non-flush mountable	
Dimensions	[mm]	20 x 14 x 48
Materials	housing: PBT glass fibre reinforced; pushbuttons: TPE-U; cover: PC glass fibre reinforced	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Teach function	yes	
Electronic lock	yes	

KQ6016



Capacitive sensor

KQ-3120NFNKG/2T/2M/US

Remarks

Pack quantity

1 pcs.


Electrical connection - plug

Cable: 2 m, PVC, Ø 2.9 mm; 3 x 0.14 mm²

Connector: 1 x M12; coding: A



Connection



4: OUT / IO-Link