

MG5002




Magnetic sensor

MGA3070-BPKG

Article no longer available - archive entry

Alternative articles: MGS201

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	70; (referred to magnet M 4.0)
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 50

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Reverse polarity protection	yes
Max. power-on delay time [ms]	2

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	300
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	70; (referred to magnet M 4.0)
--------------------	--------------------------------

Accuracy / deviations

Hysteresis [X01]	1...10
Repeatability [X01]	1

MG5002



Magnetic sensor

MGA3070-BPKG

Operating conditions

Ambient temperature	[°C]	-25...75
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)

Mechanical data

Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 50
Thread designation		M18 x 1
Materials		brass nickel-plated; sensing face: plastics

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 2 m, PUR / PVC; 3 x 0.25 mm²

Connection



BN = Core colours :
brown
BU = blue
BK = black