


Cylinder sensor for tie-rod cylinder

MKZ3000-BPKG/5M

Article no longer available - archive entry



1 sensing face



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	30 x 30 x 23

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Reverse polarity protection	yes
Max. power-on delay time [ms]	2

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	300
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Response sensitivity [mT]	3
Travel speed [m/s]	< 5

MK5044



Cylinder sensor for tie-rod cylinder

MKZ3000-BPKG/5M

Accuracy / deviations		
Hysteresis	[mm]	1
Repeatability	[mm]	0.1
Operating conditions		
Ambient temperature	[°C]	-25...75
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)
Mechanical data		
Sensing face		front
Cylinder type		tie rod cylinders
Dimensions	[mm]	30 x 30 x 23
Materials		aluminium; plastics
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 5 m, PUR / PVC; 3 x 0.25 mm ²		
Connection		



BN = Core colours :
brown
BU = blue
BK = black