


Through-beam sensor transmitter

OGS-00KG/US



Product characteristics

Type of light	red light
Housing	threaded type

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	20
Protection class	III
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	645

Detection zone

Transmitter / receiver	transmitter
Range [m]	< 8
Range adjustable	no
Max. light spot diameter [mm]	600
Light spot dimensions refer to	at maximum range

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 67; (in conjunction with a corresponding connector)

Tests / approvals

EMC	EN 60947-5-2
MTTF [ANN]	1899

Mechanical data

Weight [g]	14.3
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 44
Thread designation	M18 x 1

OGS100



Through-beam sensor transmitter

OGS-00KG/US

Materials	housing: ABS	
Lens material	PMMA	
Displays / operating elements		
Display	operation	1 x LED, green
Аксессуары		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A



Connection

