


MQ2002



Magnetic sensor

MQ23005BBPKG/B/AM/0,3M/ZH/US

Article no longer available - archive entry



- 1 LED yellow
- 2 LED green



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	5
Housing	rectangular
Dimensions [mm]	20 x 8 x 32

Application

Media	ferrous only
-------	--------------

Electrical data

Operating voltage [V]	10...30 DC
Rated insulation voltage [V]	60
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes



Magnetic sensor

MQ23005BBPKG/B/AM/0,3M/ZH/US

Power-on delay time	[s]	< 0.3
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Max. leakage current	[mA]	0.1
Permanent current rating of switching output DC	[mA]	100
Short-time current rating of switching output	[mA]	100
Switching frequency DC	[Hz]	300
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	5
Real sensing range S_r	[mm]	$5 \pm 10 \%$
Operating distance	[mm]	0...4.05
Accuracy / deviations		
Correction factor		steel: 1
Hysteresis	[X01]	< 10
Switch point drift	[X01]	10
Repeatability	[X01]	10
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-30...85
Protection		IP 65; IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes
Shock resistance	EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance	EN 60068-2-27	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes
UL approval	Ta	-25...60 °C
	Enclosure type	Type 1
	подача напруги	Limited Voltage/Current
	UL Approval no.	C010
	File number UL	E174191

MQ2002



Magnetic sensor

MQ23005BBPKG/B/AM/0,3M/ZH/US


Mechanical data		
Weight	[g]	44.9
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	20 x 8 x 32
Materials		diecast zinc; LED window: TPU; potting: PUR

Displays / operating elements		
Display	Display operation	1 x LED, green
	switching status	1 x LED, yellow

Remarks	
Pack quantity	1 pcs.

Electrical connection
Cable: 0.3 m, PUR, Ø 4.9 mm; flame-retardant (IEC 60332-2, UL: FT2)

Connection



Connector: 1 x M12; coding: A; Locking: knurled nut, rotatable

