


Through-beam sensor receiver

OFE-FNKG/US-100

Article no longer available - archive entry

Alternative articles: OF5022

When selecting an alternative article and accessories please note that technical data may differ!



1 potentiometer

Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Special feature	Function check output
Function principle	Through-beam sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 30
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		NPN
Output function		light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Function check output		yes
Max. voltage drop of function check output	[V]	3.5
Max. current load for function check output	[mA]	10
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	320
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes



Through-beam sensor receiver


OFE-FNKG/US-100

Detection zone		
Transmitter / receiver		receiver
Range [m]		< 4
Range adjustable		yes
Operating conditions		
Ambient temperature [°C]		-25...60
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Weight [g]		0.046
Housing		threaded type
Dimensions [mm]		M12 x 1 / L = 74
Thread designation		M12 x 1
Materials		housing: brass white bronze coated
Lens material		PMMA
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red
Аксессуары		
Items supplied		lock nuts: 2
		screwdrivers
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A		
		

Through-beam sensor receiver

OFE-FNKG/US-100

Connection



2 Function check output

Diagrams and graphs

excess gain graph

