



Retro-reflective sensor

OGR-DBOA/S

Article no longer available - archive entry

No scale drawing available

Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...90 AC/DC
Protection class		II
Type of light		infrared light
Wave length	[nm]	880


Outputs

Output function		dark-on mode
Max. voltage drop switching output DC	[V]	9.5
Max. voltage drop switching output AC	[V]	9.5
Minimum load current	[mA]	10
Max. leakage current	[mA]	5
Permanent current rating of switching output AC	[mA]	250
Permanent current rating of switching output DC	[mA]	50
Short-time current rating of switching output	[mA]	900; (10 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	70

**Retro-reflective sensor**

OGR-DBOA/S

Short-circuit protection	no	
Overload protection	no	
Detection zone		
Range	[m]	< 2.5; (Prismatic reflector Ø 80 E20005)
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67	
Mechanical data		
Housing	threaded type	
Dimensions	[mm]	M18 x 1
Thread designation	M18 x 1	
Materials	brass nickel-plated	
Lens material	glass	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Аксессуары		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 2 m, PVC; 2 x 0.5 mm²		
Connection		



BN = Core colours :
brown
BU = blue