




Inductive NAMUR sensor

IEA2001-N/20M/1D/1G



Product characteristics	
Electrical design	NAMUR
Output function	normally closed
Sensing range [mm]	1
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 30
Electrical data	
Connection to switching amplifiers	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC [V]	8.2; (1kΩ)
Supply voltage DC [V]	7.5...30; (when used outside the hazardous area)
Current consumption [mA]	< 1; (disabled; conductive: > 2,1)
Outputs	
Electrical design	NAMUR
Output function	normally closed
Permanent current rating of switching output DC [mA]	30; (when used outside the hazardous area)
Switching frequency DC [Hz]	2000
Detection zone	
Sensing range [mm]	1
Real sensing range Sr [mm]	1 ± 10 %
Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10
Operating conditions	
Ambient temperature [°C]	-20...70
Protection	IP 67
Tests / approvals	
Approval	PTB 01 ATEX 2191; BVS 04 ATEX E 153 X; IECEx BVS 06.0003X
ATEX marking	Ex II 1G Ex ia IIC T6 Ga Ta -20...70°C

NE5012



Inductive NAMUR sensor

IEA2001-N/20M/1D/1G

		II 1G Ex ia IIC T5 Ga Ta -20...80°C
		II 1D Ex ia IIIC T20090°C Da Ta: -20...70°C
		II 1D Ex ia IIIC T200100° C Da Ta: -20...80°C
EMC	EN 60947-5-6	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)
MTTF	[ANN]	4816


Safety classification		
Max. internal capacitance	[nF]	83
Max. internal inductance	[µH]	87

Mechanical data		
Weight	[g]	342.2
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 30
Thread designation		M8 x 1
Materials		brass special coating; sensing face: PBT

Аксессуары		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Cable: 20 m, PVC; 2 x 0.14 mm²		
Connection		



BN = Core colours : brown
BU = blue