




Inductive NAMUR sensor

IIA2015-N/10M/1D/1G/2G

Article no longer available - archive entry



Product characteristics

Electrical design	NAMUR
Output function	normally closed
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 41

Electrical data

Connection to switching amplifiers	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC [V]	8.2; (1kΩ)
Supply voltage DC [V]	7.5...30; (when used outside the hazardous area)
Current consumption [mA]	< 1; (disabled; conductive: > 2,1)
Protection class	III

Outputs

Electrical design	NAMUR
Output function	normally closed
Permanent current rating of switching output DC [mA]	30; (when used outside the hazardous area)
Switching frequency DC [Hz]	200

Detection zone

Sensing range [mm]	15
Real sensing range Sr [mm]	15 ± 10 %

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [X01]	1...15
Switch point drift [X01]	-10...10

Operating conditions


Ambient temperature [°C]	-20...80
--------------------------	----------



Inductive NAMUR sensor

IIA2015-N/10M/1D/1G/2G

Protection	IP 67	
Tests / approvals		
Approval	PTB 01 ATEX 2191; BVS 04 ATEX E153; TIIS TC16109	
ATEX marking	 II 1D Ex iaD 20 T 90°C Ta: -20...70°C	
	 II 1D Ex iaD 20 T 100°C Ta: -20...80°C	
	 II 1G Ex ia IIB T6 Ta: -20...55°C	
	 II 1G Ex ia IIB T5 Ta: -20...65°C	
	 II 2G Ex ia IIC T6 Ta: -20...70°C	
	 II 2G Ex ia IIC T5 Ta: -20...80°C	
EMC	EN 60947-5-6	
Shock/vibration resistance	30 g (11 ms) / 10-55 Hz (1 mm)	
Safety classification		
Max. internal capacitance	[nF]	147
Max. internal inductance	[μH]	118
Mechanical data		
Weight	[g]	0.518
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M30 x 1.5 / L = 41
Thread designation	M30 x 1.5	
Materials	brass special coating; sensing face: PBT	
Аксессуары		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 10 m, PVC; 2 x 0.5 mm²		
Connection		



BN = Core colours :
brown
BU = blue