



Induktiver NAMUR-Sensor

IS-2002-N/1D/1G/2G



Product characteristics		
Electrical design		NAMUR
Output function		normally closed
Sensing range	[mm]	2
Housing		rectangular
Dimensions	[mm]	28 x 10 x 16
Electrical data		
Connection to switching amplifiers		yes
Switching amplifiers		connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC	[V]	8.2; (1kΩ)
Supply voltage DC	[V]	7.5...30; (when used outside the hazardous area)
Current consumption	[mA]	< 1; (disabled; conductive: > 2,1)
Protection class		III
Outputs		
Electrical design		NAMUR
Output function		normally closed
Permanent current rating of switching output DC	[mA]	30; (when used outside the hazardous area)
Switching frequency DC	[Hz]	800
Detection zone		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[X01]	1...15


NS5003



Induktiver NAMUR-Sensor

IS-2002-N/1D/1G/2G

Switch point drift	[X01]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-20...70	
Protection		IP 67	
Tests / approvals			
Approval		PTB 02 ATEX 2217; BVS 04 ATEX E 153 X; IECEX BVS 06.0003X	
ATEX marking		 II 1G Ex ia IIB T6 Ga Ta -20...70°C	
		 II 2G Ex ia IIC T6 Gb Ta -20...70°C	
		 II 1D Ex ia IIIC T20090°C Da Ta: -20...70°C	
		 II 1D Ex ia IIIC T200100° C Da Ta: -20...80°C	
EMC		EN 60947-5-6	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)	
MTTF	[ANN]	4494	
Safety classification			
Max. internal capacitance	[nF]	80	
Max. internal inductance	[µH]	110	
Mechanical data			
Weight	[g]	79.5	
Housing		rectangular	
Mounting		flush mountable	
Dimensions	[mm]	28 x 10 x 16	
Materials		PBT	
Displays / operating elements			
Display	switching status	1 x LED, red	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Cable: 2 m, PVC; 2 x 0.14 mm²			
Connection			



BN = Core colours : brown
BU = blue