


Diffuse reflection sensor

OITGFNKG

Article no longer available - archive entry



Product characteristics

Housing	threaded type
---------	---------------

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	15; ((24 V))
Protection class		II
Reverse polarity protection		yes

Outputs

Electrical design		NPN
Output function		light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	80
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	< 80
-------	------	------



Diffuse reflection sensor

OITGFNKG

Range adjustable	yes
------------------	-----

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 65

Mechanical data

Housing	threaded type
Dimensions [mm]	M30 x 1.5
Thread designation	M30 x 1.5

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied	lock nuts: 2
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

...2.5 mm²; Cable sheath: Ø 7...13 mm; Cable gland: M20 X 1.5

Connection

