




Fibre-optic amplifier

OO5-FPKG/M16/GL6



1 mounting on DIN rail



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Special feature		Function check output
Electrical data		
Operating voltage	[V]	12...36 DC
Current consumption	[mA]	50; ((24 V))
Max. power consumption	[VA]	1.2
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	630
Outputs		
Electrical design		PNP
Output function		light-on/dark-on mode; (programmable)



Fibre-optic amplifier

00F-FPKG/M16/GL6

Max. voltage drop switching output DC	[V]	2
Function check output		yes
Max. current load for function check output	[mA]	200
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	1000
Notes on switching frequency	[Hz]	typical
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Time function	[s]	0.001...0.1

Detection zone

Range	[m]	< 0.4; (Through-beam sensor)
Range	[mm]	0...200; (Diffuse reflection sensor)
Range adjustable		yes

Software / programming

Parameter setting options	automatic and manual switch point setting; logic functions AND, OR; second switch point
---------------------------	---

Operating conditions

Ambient temperature	[°C]	-20...60
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Weight	[g]	548.5
Housing		rectangular
Dimensions	[mm]	76.5 x 123.9 x 70.7
Number of channels		6
Fibre optic connection		FE-00 / FT-00
Materials		housing: ABS; display window: PMMA; LED window: SEPS; cover: diecast zinc plastic coated (PA)
Lens alignment		side lens

Displays / operating elements

Display		full graphic LCD display, rotation of the display by 180° possible language selection (German, English, French)
	switching status	6 x LED, yellow
Electronic lock		yes

Аксессуары

Items supplied	rail: 1 x 113 mm, EN 60715
----------------	----------------------------

Remarks


Remarks	operating voltage "supply class 2" according to cULus
Pack quantity	1 pcs.

Fibre-optic amplifier


00F-FPKG/M16/GL6

Electrical connection

Connector: 1 x M16



Connection



E: Out 1
P: Out 2
S: Out 3
G: Out 4
C: Out 5
T: Out 6

O Function check output