


Retro-reflective sensor

OSP-FNKG

Article no longer available - archive entry

Alternative articles: OA5106

When selecting an alternative article and accessories please note that technical data may differ!



- 1 potentiometer timer
- 2 potentiometer sensitivity receiver in upper lens
- transmitter in lower lens

Product characteristics

Type of light	red light
Housing	rectangular

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage [V]	10...55 DC
Current consumption [mA]	25; ((24 V))
Protection class	II
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	660

Outputs

Electrical design	NPN
Output function	light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	100



Retro-reflective sensor

OSP-FNKG

Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range [m]	< 6; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Polarisation filter available	yes

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

Mechanical data

Housing	rectangular
Dimensions [mm]	80 x 28 x 95
Materials	PPO modified
Lens material	glass

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied	Angle bracket screwdrivers
----------------	-------------------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

terminals: ...1.5 mm²; Cable sheath: Ø 7...13 mm

Connection

