


Fibre-optic amplifier

OUF-DPKG/US-100-DPO



Product characteristics

Type of light	infrared light
Housing	rectangular

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	35; ((24 V))
Protection class	III
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	880

Outputs

Electrical design	PNP
Output function	dark-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	100
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range [m]	0...0.12; (Through-beam sensor)
Range [mm]	0...40; (Diffuse reflection sensor)
Range adjustable	yes

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 65



Fibre-optic amplifier

OUF-DPKG/US-100-DPO

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[ANN]	583

Mechanical data

Weight	[g]	75
Housing		rectangular
Dimensions	[mm]	28 x 16 x 56
Materials		PPO modified
Lens material		glass
Lens alignment		side lens

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары

Items supplied	Angle bracket: 1, E20211
	screwdrivers

Remarks


Remarks	dark-on mode corresponds to the NO output function for through-beam fibre optics
	corresponds to the NC output function for diffuse-reflection fibre optics
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



**Fibre-optic amplifier**

OUF-DPKG/US-100-DPO

Diagrams and graphs

excess gain graph

