


Diffuse reflection sensor

OUT-DNKG/US-100-DNO

Article no longer available - archive entry



receiver in upper lens
transmitter in lower lens

Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...50 DC
Current consumption	[mA]	35; ((24 V))
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		NPN
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	< 200; (white paper 200 x 200 mm)
Range adjustable		yes
Max. light spot diameter	[mm]	180
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...80
---------------------	------	----------



Diffuse reflection sensor

OUT-DNKG/US-100-DNO

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	rectangular
Dimensions [mm]	28 x 16 x 51
Materials	PPO modified
Lens material	glass

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Аксессуары


Items supplied	Angle bracket
----------------	---------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection

