




Through-beam sensor transmitter

OGS-00KG/6M



Product characteristics

Type of light	red light
Housing	threaded type

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15
Protection class	II
Reverse polarity protection	yes
Type of light	red light

Detection zone

Transmitter / receiver	transmitter
Range [m]	< 20
Range adjustable	no
Max. light spot diameter [mm]	800
Light spot dimensions refer to	at maximum range

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 65; IP 67; IP 68; IP 69K

Tests / approvals

EMC	EN 60947-5-2
MTTF [ANN]	755

Mechanical data

Weight [g]	245.8
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 68.6
Thread designation	M18 x 1
Materials	housing: stainless steel (1.4404 / 316L); Sealing: EPDM

OGS301



Through-beam sensor transmitter

OGS-00KG/6M

Lens material	PMMA
---------------	------

Displays / operating elements

Display	operation	1 x LED, green
---------	-----------	----------------

Аксессуары

Items supplied	lock nuts: 2
----------------	--------------

Remarks


Remarks	operating voltage "supply class 2" according to cULus
---------	---

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m, PVC; 3 x 0.34 mm²

Connection



BN = Core colours :
BU = brown
blue



Through-beam sensor transmitter

OGS-OOKG/6M

Diagrams and graphs

excess gain graph

