


Retro-reflective sensor

OER-V/OET-V/10M

Article no longer available - archive entry



Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

Electrical data

Connection to switching amplifiers	yes
Switching amplifiers	Connection to switching amplifiers OV5012, OV0010
Protection class	III
Type of light	infrared light
Wave length [nm]	950

Outputs

Short-circuit protection	no
Overload protection	no

Detection zone

Range referred to prismatic reflector [m]	0.03...0.2; (Prismatic reflector Ø 80 E20005)
Range [mm]	< 15; (white paper 200 x 200 mm)

Operating conditions

Ambient temperature [°C]	0...70
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2
-----	--------------



Retro-reflective sensor

OER-V/OET-V/10M

MTTF	[ANN]	5623
------	-------	------

Mechanical data		
-----------------	--	--

Weight	[g]	0.2
Housing		threaded type
Dimensions	[mm]	M8 x 1
Thread designation		M8 x 1
Materials		brass nickel-plated

Аксессуары		
------------	--	--

Items supplied		lock nuts: 2
----------------	--	--------------


Remarks		
---------	--	--

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection		
-----------------------	--	--

Cable: 10 m; 2 x 0.14 mm²

Connection		
------------	--	--



1 = transmitter
 2 = receiver
 Core colours :
 RD = red
 WH = white
 screen = screen