



Through-beam sensor receiver

OFE-FPKG/US-100



1 potentiometer



Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Special feature	Function check output
Function principle	Through-beam sensor

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 30
Protection class	II
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	880

Outputs

Electrical design	PNP
Output function	light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC [V]	2.5
Function check output	yes
Max. voltage drop of function check output [V]	3.5
Max. current load for function check output [mA]	10
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	320
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Transmitter / receiver	receiver
Range [m]	< 4



Through-beam sensor receiver

OFE-FPKG/US-100

Range adjustable	yes
------------------	-----

Operating conditions

Ambient temperature	[°C]	-25...60
---------------------	------	----------

Protection	IP 65
------------	-------

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

MTTF	[ANN]	652
------	-------	-----

Mechanical data

Weight	[g]	40.7
--------	-----	------

Housing	threaded type
---------	---------------

Dimensions	[mm]	M12 x 1 / L = 74
------------	------	------------------

Thread designation	M12 x 1
--------------------	---------

Materials	housing: brass white bronze coated
-----------	------------------------------------

Lens material	PMMA
---------------	------

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

	operation	1 x LED, green
--	-----------	----------------

	function	1 x LED, red
--	----------	--------------

Аксессуары

Items supplied	lock nuts: 2
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Through-beam sensor receiver

OFE-FPKG/US-100

Connection



2 Function check output

Diagrams and graphs

excess gain graph

