


PA3528



Pressure transmitter with ceramic measuring cell

PA-,25BRBG14-A-ZVG/US/ IV



1      Sealing



| Product characteristics      |  |                                                              |                 |                 |            |
|------------------------------|--|--------------------------------------------------------------|-----------------|-----------------|------------|
| Number of inputs and outputs |  | Number of analogue outputs: 1                                |                 |                 |            |
| Measuring range              |  | 0...0.25 bar                                                 | 0...250 mbar    | 0...100.3 inH2O | 0...25 kPa |
| Process connection           |  | threaded connection G 1/4 external thread internal thread:M5 |                 |                 |            |
| Application                  |  |                                                              |                 |                 |            |
| Special feature              |  | Gold-plated contacts                                         |                 |                 |            |
| Application                  |  | for industrial applications                                  |                 |                 |            |
| Media                        |  | liquids and gases                                            |                 |                 |            |
| Medium temperature           |  | [°C] -25...90; (on request: -40...90 °C)                     |                 |                 |            |
| Min. bursting pressure       |  | 30000 mbar                                                   | 12030 inH2O     | 3000 kPa        |            |
| Pressure rating              |  | 6000 mbar                                                    | 2400 inH2O      | 600 kPa         |            |
| Type of pressure             |  | relative pressure                                            |                 |                 |            |
| Electrical data              |  |                                                              |                 |                 |            |
| Operating voltage            |  | [V]                                                          | 9.6...32 DC     |                 |            |
| Min. insulation resistance   |  | [MΩ]                                                         | 100; (500 V DC) |                 |            |
| Protection class             |  | III                                                          |                 |                 |            |
| Reverse polarity protection  |  | yes                                                          |                 |                 |            |
| Inputs / outputs             |  |                                                              |                 |                 |            |
| Number of inputs and outputs |  | Number of analogue outputs: 1                                |                 |                 |            |
| Outputs                      |  |                                                              |                 |                 |            |
| Total number of outputs      |  | 1                                                            |                 |                 |            |
| Output signal                |  | analogue signal                                              |                 |                 |            |
| Number of analogue outputs   |  | 1                                                            |                 |                 |            |
| Analogue current output      |  | [mA]                                                         | 4...20          |                 |            |



## Pressure transmitter with ceramic measuring cell

PA-,25BRBG14-A-ZVG/US/ IV

|                                    |                           |                                                                                           |              |                   |            |
|------------------------------------|---------------------------|-------------------------------------------------------------------------------------------|--------------|-------------------|------------|
| Max. load                          | [Ω]                       | 720; (Ub = 24 V; (Ub - 9,6 V) / 20 mA)                                                    |              |                   |            |
| Overload protection                |                           | yes                                                                                       |              |                   |            |
| Measuring/setting range            |                           |                                                                                           |              |                   |            |
| Measuring range                    |                           | 0...0.25 bar                                                                              | 0...250 mbar | 0...100.3 inH2O   | 0...25 kPa |
| Accuracy / deviations              |                           |                                                                                           |              |                   |            |
| Repeatability                      | [X21]                     | < 0,1; (with temperature fluctuations < 10 K)                                             |              |                   |            |
| Characteristics deviation          | [X21]                     | < ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting) |              |                   |            |
| Long-term stability                | [X21]                     | < ± 0,05; (per 6 months)                                                                  |              |                   |            |
| Temperature coefficient zero point | [X22]                     | < ± 0,2; (0...80 °C)                                                                      |              |                   |            |
| Temperature coefficient span       | [X22]                     | < ± 0,3; (0...80 °C)                                                                      |              |                   |            |
| Response times                     |                           |                                                                                           |              |                   |            |
| Step response time analogue output | [ms]                      | 3                                                                                         |              |                   |            |
| Operating conditions               |                           |                                                                                           |              |                   |            |
| Ambient temperature                | [°C]                      | -25...80                                                                                  |              |                   |            |
| Storage temperature                | [°C]                      | -40...100                                                                                 |              |                   |            |
| Protection                         |                           | IP 65                                                                                     |              |                   |            |
| Tests / approvals                  |                           |                                                                                           |              |                   |            |
| EMC                                | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD                                                                         |              |                   |            |
|                                    | EN 61000-4-3 HF radiated  | 30 V/m                                                                                    |              |                   |            |
|                                    | EN 61000-4-4 Burst        | 2 kV                                                                                      |              |                   |            |
|                                    | EN 61000-4-6 HF conducted | 10 V                                                                                      |              |                   |            |
|                                    | radiation of interference | according to the automotive directive 2004/104/EC                                         |              |                   |            |
|                                    | CISPR 25                  |                                                                                           |              |                   |            |
|                                    | immunity                  | according to the automotive directive 2004/104/EC                                         |              |                   |            |
|                                    | ISO 11452-2 HF radiated   | 100 V/m                                                                                   |              |                   |            |
| Shock resistance                   | ISO 7637-2 pulse          | severity level 4                                                                          |              |                   |            |
|                                    | DIN EN 60068-2-27         | 50 g (11 ms)                                                                              |              |                   |            |
| Vibration resistance               | DIN EN 61373              | category 3                                                                                |              |                   |            |
|                                    | DIN EN 60068-2-6          | 20 g (10...2000 Hz)                                                                       |              |                   |            |
| MTTF                               | DIN EN 61373              | category 2                                                                                |              |                   |            |
|                                    | [ANN]                     | 514                                                                                       |              |                   |            |
| Pressure Equipment Directive       |                           | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request     |              |                   |            |
| Railway applications               |                           | DIN EN 50155 / IEC 60571                                                                  |              | Klasse T3, C1, S1 |            |
| Mechanical data                    |                           |                                                                                           |              |                   |            |
| Weight                             | [g]                       | 217                                                                                       |              |                   |            |
| Materials                          |                           | stainless steel (1.4404 / 316L); FKM; PA; EPDM/X                                          |              |                   |            |
| Materials (wetted parts)           |                           | stainless steel (1.4305 / 303); ceramics; Sealing: FKM DIN 3869-14                        |              |                   |            |
| Min. pressure cycles               |                           | 100 million                                                                               |              |                   |            |
| Process connection                 |                           | threaded connection G 1/4 external thread internal thread:M5                              |              |                   |            |
| Restrictor element integrated      |                           | no (can be retrofitted)                                                                   |              |                   |            |
| Remarks                            |                           |                                                                                           |              |                   |            |
| Pack quantity                      |                           | 1 pcs.                                                                                    |              |                   |            |

# PA3528



## Pressure transmitter with ceramic measuring cell

PA-,25BRBG14-A-ZVG/US/ IV

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection

