


Retro-reflective sensor

OGR-DPKG/US-100-DPS



Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

Electrical data

Operating voltage [V]	10...55 DC
Current consumption [mA]	10; ((24 V))
Protection class	II
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	880

Outputs

Electrical design	PNP
Output function	dark-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	160
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range referred to prismatic reflector [m]	3; (Prismatic reflector Ø 80 E20005)
---	--------------------------------------

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 65

OG5027



Retro-reflective sensor

OGR-DPKG/US-100-DPS

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[ANN]	826

Mechanical data		
Weight	[g]	76.9
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 80
Thread designation		M18 x 1
Materials		brass nickel-plated
Lens material		PMMA


Displays / operating elements		
Display	switching status	1 x LED, yellow

Аксессуары		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection		
-----------------------	--	--

Connector: 1 x M12; coding: A



Connection		
------------	--	--

