



Retro-reflective sensor

OGP-FPKG/US-100/MIT 90GRAD WKL

Article no longer available - archive entry

Alternative articles: OG5126

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Product characteristics

Type of light	red light
Housing	threaded type

Application

Special feature	Gold-plated contacts
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 32
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Max. voltage drop of function check output	[V]	3.5
Max. current load for function check output	[mA]	10
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500

**Retro-reflective sensor**

OGP-FPKG/US-100/MIT 90GRAD WKL

Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range [m]	< 2.5; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	threaded type
Dimensions [mm]	M18 x 1
Thread designation	M18 x 1
Materials	PBT
Lens material	PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Аксессуары

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated






Retro-reflective sensor

OGP-FPKG/US-100/MIT 90GRAD WKL

Connection



2

Function check output