




Flush pressure sensor

PF-001BRES30-MFRKG/US/ /P

phase-out article
Discontinuation date: 03/31/2024

Alternative articles: PI1009 or PI1707
When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.
no more adapters available as accessories



- 1 7-segment LED display
- 2 programming button
- 3 Aseptoflex sealing edge
- 4 Aseptoflex thread



Product characteristics				
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1			
Measuring range	-0.05...1 bar	-50...1000 mbar	-0.7...14.5 psi	-5...100 kPa
Process connection	threaded connection Aseptoflex external thread Aseptoflex			

Application			
Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	freely rotatable housing 350°		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...80		
Min. bursting pressure	30000 mbar	450 psi	3000 kPa
Pressure rating	10000 mbar	145 psi	1000 kPa
Type of pressure	relative pressure		



Flush pressure sensor

PF-001BRES30-MFRKG/US/ /P

No dead space	yes
---------------	-----

Electrical data

Operating voltage [V]	20...30 DC
Current consumption [mA]	< 60
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	0.2
Integrated watchdog	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	< 170
Number of analogue outputs	1
Analogue current output [mA]	4...20; (scalable 1:4)
Max. load [Ω]	(U _b - 10 V) / 20 mA
Analogue voltage output [V]	0...10; (scalable 1:4)
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Measuring range	-0.05...1 bar	-50...1000 mbar	-0.7...14.5 psi	-5...100 kPa
Set point SP	-45...999 mbar	-0.7...14.5 psi	-4.5...99.9 kPa	
Reset point rP	-50...994 mbar	-0.7...14.4 psi	-5...99.4 kPa	
Analogue start point	-50...749 mbar	-0.7...10.9 psi	-5...74.9 kPa	
Analogue end point	200...999 mbar	2.9...14.5 psi	20...99.9 kPa	
In steps of	1 mbar	0.1 psi	0.1 kPa	
Factory setting		SP1 = 250 mbar	rP1 = 230 mbar	
		ASP = 0 mbar	AEP = 999 mbar	

Accuracy / deviations

Repeatability [X21]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation [X21]	< ± 0,6; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)
Linearity deviation [X21]	< ± 0,5; (Turn down 1:1)



Flush pressure sensor

PF-001BRES30-MFRKG/US/ /P

Hysteresis deviation	[X21]	< ± 0,1; (Turn down 1:1)
Long-term stability	[X21]	< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point	[X22]	< ± 0,1; (0...80 °C)
Temperature coefficient span	[X22]	< ± 0,2; (0...80 °C)
Response times		
Response time	[ms]	< 3
Damping process value dAP	[s]	0...4
Damping for the analogue output dAA in steps	[s]	0 - 0,1 - 0,5 - 2
Max. response time analogue output	[ms]	3
Software / programming		
Parameter setting options		hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	181
Mechanical data		
Weight	[g]	279.75
Materials		stainless steel (1.4404 / 316L); PBT; PC; PEI; EPDM/X; FKM
Materials (wetted parts)		ceramics (99.9 % Al ₂ O ₃); stainless steel (1.4435 / 316L); surface characteristics: Ra < 0,4 / Rz 4; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection Aseptoflex external thread Aseptoflex
Displays / operating elements		
Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display
Display unit		mbar; psi; kPa
Remarks		
Remarks		The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.
Notes		Please do not use for new projects.; no more adapters available as accessories
Pack quantity		1 pcs.



Flush pressure sensor




PF-001BRES30-MFRKG/US/ /P

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1
OUT2

switching output
switching output
analogue output