




Flush pressure sensor

PF-001-REA01-QFPKG/US/ /P

Article no longer available - archive entry

Alternative articles: PF2657
When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
- 2 programming button



Product characteristics	
Number of inputs and outputs	Number of digital outputs: 2
Measuring range [bar]	0...1
Process connection	threaded connection G 1 external thread
Application	
Special feature	Gold-plated contacts
Application	flush mountable for the food and beverage industry
Installation	freely rotatable housing 350°
Media	viscous media and liquids with suspended particles; liquids and gases
Medium temperature [°C]	-25...80
Min. bursting pressure [bar]	30
Pressure rating [bar]	10
Type of pressure	relative pressure
No dead space	yes



Flush pressure sensor

PF-001-REA01-QFPKG/US/ /P

Electrical data											
Operating voltage	[V]	18...30 DC									
Current consumption	[mA]	< 60									
Min. insulation resistance	[MΩ]	100; (500 V DC)									
Protection class		III									
Reverse polarity protection		yes									
Power-on delay time	[s]	0.2									
Integrated watchdog		yes									
Inputs / outputs											
Number of inputs and outputs		Number of digital outputs: 2									
Outputs											
Total number of outputs		2									
Output signal		switching signal									
Electrical design		PNP									
Number of digital outputs		2									
Output function		normally open / normally closed; (parameterisable)									
Max. voltage drop switching output DC	[V]	2									
Permanent current rating of switching output DC	[mA]	250									
Short-circuit protection		yes									
Type of short-circuit protection		pulsed									
Overload protection		yes									
Measuring/setting range											
Measuring range	[bar]	0...1									
Set point SP	[bar]	0.02...1									
Reset point rP	[bar]	0.01...0.99									
In steps of	[bar]	0.01									
Accuracy / deviations											
Switch point accuracy	[X16]	< ± 1									
Repeatability	[X16]	< ± 0,25; (with temperature fluctuations < 10 K)									
Temperature drift per 10 K		< ± 0.3									
Response times											
Switching frequency for a given set response time of one output	Response time (dAP)	[ms]	3	6	10	17	30	60	125	250	500
	Switching frequency	[Hz]	170	80	50	30	16	8	4	2	1
Response time	[ms]	at rectangular pressure characteristic; switch point (SPx) = 70 %; reset point (rPx) = 30 %									
Delay time programmable dS, dr	[s]	0, 0,2,...10, 11,...50									
Software / programming											
Adjustment of the switch point		programming button									
Parameter setting options		hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping									

PF7657



Flush pressure sensor

PF-001-REA01-QFPKG/US/ /P

Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data	
Materials	EPDM/X; FKM; PA; PBT; PC; PTFE; stainless steel (1.4404 / 316L)
Materials (wetted parts)	ceramics; PTFE; stainless steel (1.4404 / 316L)
Min. pressure cycles	100 million
Process connection	threaded connection G 1 external thread

Displays / operating elements		
Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

