



Retro-reflective sensor

OLP-FPKG/LS-400

Article no longer available - archive entry

Alternative articles: O5P500 + E21122

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Product characteristics

Type of light	red light
Housing	rectangular

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 37
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100; (200 (...50 °C))
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed

**Retro-reflective sensor**

OLP-FPKG/LS-400

Overload protection	yes	
Detection zone		
Range	[m]	0.3...5; (Prismatic reflector Ø 80 E20005)
Range referred to prismatic reflector	[m]	0.3...5; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes	
Polarisation filter available	yes	
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	rectangular	
Dimensions	[mm]	75 x 27 x 62
Materials	PBT	
Lens material	PMMA	
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x 7/8"		