




Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS



- 1 potentiometer sensitivity
- 2 output function switch



Product characteristics

Type of light	red light
---------------	-----------

Electrical data

Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 30
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (selectable)
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	5000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Diameter of the smallest detectable object	[mm]	0.3
--	------	-----

Interfaces

Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9



Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS

Profiles	Smart Sensor: Device Identification; Device Diagnosis; Teach Channel; Switching Channel; Process Data Variable	
SIO mode	yes	
Required master port type	A	
Min. process cycle time [ms]	3.2	
Supported DeviceIDs	Type of operation	DeviceID
	default	378

Operating conditions		
Ambient temperature [°C]	-25...60	
Protection	IP 67	

Tests / approvals		
EMC	EN 60947-5-2	
MTTF [ANN]	709	

Mechanical data		
Weight [g]	74	
Dimensions [mm]	40 x 10 x 50	
Fork depth D [mm]	25	
Fork width W [mm]	20	
Materials	housing: diecast zinc black anodised; lens: glass	

Displays / operating elements		
Display	switching status	1 x LED, yellow

Remarks		
Remarks	operating voltage "supply class 2" according to cULus	
Pack quantity	1 pcs.	

Electrical connection


Connector: 1 x M8; coding: A



Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS

Connection



4

OUT / IO-Link