


OR0003



Through-beam sensor transmitter

ORS-V



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Connection to switching amplifiers	yes
Switching amplifiers	Connection to switching amplifiers OV5012, OV0010
Type of light	infrared light
Wave length [nm]	950

Outputs

Short-circuit protection	no
Overload protection	no

Detection zone

Transmitter / receiver	transmitter
Range [m]	< 2

Operating conditions

Ambient temperature [°C]	-20...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2
MTTF [ANN]	57078


OR0003



Through-beam sensor transmitter

ORS-V

Mechanical data	
Weight	[g] 59.5
Housing	rectangular
Materials	PPO modified
Lens alignment	side lens
Аксессуары	
Items supplied	Angle bracket: 1, E20212
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Cable: 2 m; 1 x 0.14 mm²	
Connection	



RD = Core colours :
screen = red
screen