




Retro-reflective sensor

OSR-FBOA



Product characteristics		
Type of light		infrared light
Housing		rectangular
Application		
Function principle		Retro-reflective sensor
Electrical data		
Operating voltage	[V]	20...250 AC/DC
Protection class		II
Reverse polarity protection		no
Type of light		infrared light
Wave length	[nm]	950
Outputs		
Output function		light-on/dark-on mode; (programmable)
Minimum load current	[mA]	15
Max. leakage current	[mA]	6
Permanent current rating of switching output AC	[mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC	[mA]	250; (350 (...50 °C))
Short-time current rating of switching output	[mA]	2200; (10 ms / 0,5 Hz)
Switching frequency AC	[Hz]	250
Switching frequency DC	[Hz]	250



Retro-reflective sensor

OSR-FBOA

Short-circuit proof	no
Overload protection	no
Detection zone	
Range referred to prismatic reflector [m]	10; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 65
Tests / approvals	
EMC	EN 60947-5-2
MTTF [ANN]	302
Mechanical data	
Weight [g]	268
Housing	rectangular
Dimensions [mm]	80 x 28 x 95
Materials	PPO modified
Lens material	glass
Lens alignment	side lens
Displays / operating elements	
Display	switching status 1 x LED, yellow
Electrical connection	
Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting
Аксессуары	
Items supplied	Angle bracket: 1, E20210 screwdrivers
Remarks	
Remarks	Recommendation: Check the safe functioning of the unit after a short circuit.
Pack quantity	1 pcs.




Retro-reflective sensor

OSR-FBOA

Electrical connection

terminals: ...1.5 mm²; Cable gland: M20 X 1.5

Connection



Note : miniature fuse to IEC60127-2 sheet 1 $\leq$ 2 A fast acting