




Flush pressure sensor with display

PI-010-REB34-MFRKG/US/ IP

Article no longer available - archive entry

Alternative articles: PI2994

When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
- 2 programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	-0.5...10 bar	-7...145 psi	-50...1000 kPa
Process connection	threaded connection G 3/4 external thread		

Application

Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	freely rotatable housing 350°		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	150 bar	2175 psi	15000 kPa
Pressure rating	50 bar	725 psi	5000 kPa
Type of pressure	relative pressure		
No dead space	yes		

Electrical data

Operating voltage [V]	20...30 DC
-----------------------	------------



Flush pressure sensor with display

PI-010-REB34-MFRKG/US/ /P

Current consumption	[mA]	< 60
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.2
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	< 170
Number of analogue outputs	1
Analogue current output [mA]	4...20; (scalable 1:4)
Max. load [Ω]	(U _b - 10 V) / 20 mA
Analogue voltage output [V]	0...10; (scalable 1:4)
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Measuring range	-0.5...10 bar	-7...145 psi	-50...1000 kPa
Set point SP	-0.45...9.99 bar	-7...145 psi	-45...999 kPa
Reset point rP	-0.5...9.94 bar	-7...144 psi	-50...994 kPa
Analogue start point	-0.5...7.49 bar	-7...109 psi	-50...749 kPa
Analogue end point	2...9.99 bar	29...145 psi	200...999 kPa
In steps of	0.01 bar	1 psi	1 kPa

Accuracy / deviations

Repeatability	[X21]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation	[X21]	< ± 0,6; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)
Linearity deviation	[X21]	< ± 0,5; (Turn down 1:1)
Hysteresis deviation	[X21]	< ± 0,1; (Turn down 1:1)
Long-term stability	[X21]	< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point	[X22]	< ± 0,1; (0...80 °C)
Temperature coefficient span	[X22]	< ± 0,2; (0...80 °C)



Flush pressure sensor with display

PI-010-REB34-MFRKG/US/ IP

Response times		
Response time	[ms]	< 3
Damping process value dAP	[s]	0...4
Damping for the analogue output dAA in steps	[s]	0 - 0,1 - 0,5 - 2
Max. response time analogue output	[ms]	3
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span	
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Materials	stainless steel (1.4404 / 316L); PBT; PC; PEI; EPDM/X; FKM	
Materials (wetted parts)	stainless steel (1.4404 / 316L); ceramics (99.9 % Al2O3); PTFE; FKM	
Min. pressure cycles	100 million	
Process connection	threaded connection G 3/4 external thread	
Displays / operating elements		
Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display
Display unit	bar; psi; kPa	
Remarks		
Pack quantity	1 pcs.	

Connector: 1 x M12; coding: A; Contacts: gold-plated






Flush pressure sensor with display

PI-010-REB34-MFRKG/US/ IP

Connection



OUT1
OUT2

switching output
switching output
analogue output