




Flush pressure sensor with display

PI-001-REB34-MFRKG/US/ IP

phase-out article
Discontinuation date: 03/31/2024

Alternative articles: PM1507 + E30482 or PI1707
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1	
Measuring range	-0.05...1 bar	-50...1000 mbar
Process connection	threaded connection G 3/4 external thread	
Application		
Special feature	Gold-plated contacts	
Application	flush mountable for the food and beverage industry	
Installation	freely rotatable housing 350°	
Media	viscous media and liquids with suspended particles; liquids and gases	
Medium temperature [°C]	-25...125; (145 max. 1h)	
Min. bursting pressure [mbar]	30000	
Pressure rating [mbar]	10000	
Type of pressure	relative pressure	
No dead space	yes	



Flush pressure sensor with display

PI-001-REB34-MFRKG/US/ IP

Electrical data			
Operating voltage	[V]	18...32 DC	
Current consumption	[mA]	< 50	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	0.5	
Measuring principle		hydrostatic	
Integrated watchdog		yes	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1	
Outputs			
Total number of outputs		2	
Output signal		switching signal; analogue signal; (configurable)	
Electrical design		PNP/NPN	
Number of digital outputs		1	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	6	
Number of analogue outputs		1	
Analogue current output	[mA]	4...20, invertible; (scalable 1:4)	
Max. load	[Ω]	(Ub - 10 V) / 20 mA	
Analogue voltage output	[V]	0...10, invertible; (scalable 1:4)	
Min. load resistance	[Ω]	2000	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range		-0.05...1 bar	-50...1000 mbar
Set point SP	[mbar]	-48...1000	
Reset point rP	[mbar]	-50...998	
Analogue start point	[mbar]	-50...750	
Analogue end point	[mbar]	200...1000	
In steps of	[mbar]	1	
Factory setting		SP1 = 250 mbar	rP1 = 230 mbar
		ASP = 0 mbar	AEP = 1000 mbar
Accuracy / deviations			
Switch point accuracy	[X21]	< ± 0,2; (Turn down 1:1)	
Repeatability	[X21]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	[X21]	< ± 0,2; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)	



Flush pressure sensor with display

PI-001-REB34-MFRKG/US/ IP

Linearity deviation	[X21]	< ± 0,15; (Turn down 1:1)
Hysteresis deviation	[X21]	< ± 0,15; (Turn down 1:1)
Long-term stability	[X21]	< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point	[X22]	< ± 0,05; (0...70 °C)
Temperature coefficient span	[X22]	< ± 0,15; (0...70 °C)
Response times		
Response time	[ms]	< 100
Damping process value dAP	[s]	0.1...100
Damping for the analogue output dAA	[s]	0.1...100
Step response time analogue output	[ms]	25
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span	
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection	IP 67; IP 69K	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	163
Mechanical data		
Weight	[g]	382.5
Materials	stainless steel (1.4404 / 316L); PC; PBT; PEI; FKM; PTFE	
Materials (wetted parts)	ceramics (99.9 % Al2O3); stainless steel (1.4435 / 316L); surface characteristics: Ra < 0,4 / Rz 4; PTFE	
Min. pressure cycles	100 million	
Process connection	threaded connection G 3/4 external thread	
Displays / operating elements		
Display	Display unit	6 x, green
	switching status	LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit
Display unit	mbar; kPa; psi; inH2O; mWS; % of the span	
Remarks		
Notes	phase-out article	
Pack quantity	1 pcs.	

PI2997



Flush pressure sensor with display



PI-001-REB34-MFRKG/US/ /P

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1
OUT2

switching output
analogue output