


Fibre-optic amplifier

OUF-HNKG/US-100-DNS

Article no longer available - archive entry



Product characteristics

Type of light	infrared light
Housing	rectangular

Electrical data

Operating voltage	[V]	10...50 DC
Current consumption	[mA]	35; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		NPN
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[m]	0...0.12; (Through-beam sensor)
Range	[mm]	0...40; (Diffuse reflection sensor)
Range adjustable		yes

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2
-----	--------------



Fibre-optic amplifier

OUF-HNKG/US-100-DNS

Mechanical data		
Weight	[g]	0.075
Housing		rectangular
Dimensions	[mm]	28 x 16 x 56
Materials		PPO modified
Lens material		glass

Displays / operating elements		
Display	switching status	1 x LED, yellow

Аксессуары		
Items supplied		Angle bracket: 1, E20211
		screwdrivers


Remarks		
Remarks		light-on mode corresponds to the NC output function for through-beam fibre optics
		corresponds to the NO output function for diffuse-reflection fibre optics
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



Fibre-optic amplifier

OUF-HNKG/US-100-DNS

Diagrams and graphs

excess gain graph

