

## Safety light curtain

OYA1360-14-4-06-P-1

For 8-pole sockets the core colours are not standardised.  
Please note the wiring of the sensor and the sockets (see data sheet).



- T transmitter  
R receiver  
1 LED three-colour red / green / orange  
2 LED 2-colour yellow/blue  
3 LED 2-colour red/green



## Product characteristics

|                   |                |
|-------------------|----------------|
| Type of light     | infrared light |
| Electrical design | PNP            |
| Protection        | IP 65; IP 67   |

## Application

|                     |                                     |
|---------------------|-------------------------------------|
| Protective function | access prevention finger protection |
|---------------------|-------------------------------------|



## Safety light curtain

OYA1360-14-4-06-P-1

| Electrical data                              |                                    |                                                |
|----------------------------------------------|------------------------------------|------------------------------------------------|
| Operating voltage tolerance                  | [%]                                | 20                                             |
| Operating voltage                            | [V]                                | 24 DC                                          |
| Protection class                             |                                    | III                                            |
| Reverse polarity protection                  |                                    | yes                                            |
| Power-on delay time                          | [s]                                | < 2                                            |
| Type of light                                |                                    | infrared light                                 |
| Wave length                                  | [nm]                               | 950                                            |
| Receiver                                     |                                    |                                                |
| Current consumption                          | [mA]                               | 83                                             |
| Transmitter                                  |                                    |                                                |
| Current consumption                          | [mA]                               | 42                                             |
| Outputs                                      |                                    |                                                |
| Electrical design                            |                                    | PNP                                            |
| Number of OSSD outputs                       |                                    | 2                                              |
| Max. current load per OSSD output            | [mA]                               | 400; (24 V)                                    |
| Short-circuit protection                     |                                    | yes                                            |
| Detection zone                               |                                    |                                                |
| Protected area height                        | [mm]                               | 1360                                           |
| Resolution (detection capacity d)            | [mm]                               | 14                                             |
| Protection area width (low light intensity)  | [m]                                | 0...3                                          |
| Protection area width (high light intensity) | [m]                                | 1...6                                          |
| Response times                               |                                    |                                                |
| Response time                                | [ms]                               | 18                                             |
| Operating conditions                         |                                    |                                                |
| Applications                                 |                                    | class C to EN 60654-1 weatherproof application |
| Ambient temperature                          | [°C]                               | -10...55                                       |
| Max. relative air humidity                   | [%]                                | 95                                             |
| Protection                                   |                                    | IP 65; IP 67                                   |
| Tests / approvals                            |                                    |                                                |
| EMC                                          | IEC 61496-1                        |                                                |
| Shock resistance                             | IEC 61496-1                        |                                                |
| Vibration resistance                         | IEC 61496-1                        |                                                |
| Safety classification                        |                                    |                                                |
| ESPE type (IEC 61496-1)                      |                                    | 4                                              |
| Complies with the requirements               | ISO 13849-1: 2015 category 4, PL e |                                                |
|                                              | IEC 61508 SIL 3                    |                                                |
|                                              | IEC 62061 SIL 3                    |                                                |
| Mission time TM                              | [h]                                | 175200                                         |
| PFH                                          | [1/h]                              | 3,0E-08                                        |



Safety light curtain

OYA1360-14-4-06-P-1

| Mechanical data               |      |                                    |
|-------------------------------|------|------------------------------------|
| Weight                        | [g]  | 4570                               |
| Dimensions                    | [mm] | 1413 x 28 x 30                     |
| Materials                     |      | housing: aluminium; front pane: PC |
| Length L                      | [mm] | 1413                               |
| Displays / operating elements |      |                                    |
| Display                       |      | LED, yellow                        |
|                               |      | LED, green                         |
|                               |      | LED, red                           |
|                               |      | LED, blue                          |
|                               |      | LED, orange                        |
| Аксессуары                    |      |                                    |
| Items supplied                |      | mounting bracket: 6                |
|                               |      | slot nuts: 6                       |
|                               |      | Nuts                               |
| Remarks                       |      |                                    |
| Pack quantity                 |      | 1 pcs.                             |

Electrical connection - receiver

Connector: 1 x M12; coding: A; Maximum cable length: 100 m; for wire cross-section 0.34 mm²



Connection





## Safety light curtain

OYA1360-14-4-06-P-1

### Electrical connection - transmitter

Connector: 1 x M12; coding: A



### Connection

