


PA9060



Pressure transmitter with ceramic measuring cell

PA-600-SBR14-B-DVG/US/V



Product characteristics			
Number of inputs and outputs	Number of analogue outputs: 1		
Measuring range	0...600 bar	0...8700 psi	0...60 MPa
Process connection	threaded connection G 1/4 internal thread		
Application			
Special feature	Gold-plated contacts		
Application	for industrial applications		
Media	liquids and gases		
Conditionally suitable for	use in gases at pressures > 25 bar only on request		
Medium temperature [°C]	-25...90; (on request: -40...90 °C)		
Min. bursting pressure	1200 bar	17400 psi	120 MPa
Pressure rating	800 bar	11600 psi	80 MPa
Type of pressure	relative pressure		
Electrical data			
Operating voltage [V]	16...32 DC		
Current consumption [mA]	< 18		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		
Inputs / outputs			
Number of inputs and outputs	Number of analogue outputs: 1		
Outputs			
Total number of outputs	1		
Output signal	analogue signal		



Pressure transmitter with ceramic measuring cell

PA-600-SBR14-B-DVG/US/V

Number of analogue outputs		1		
Analogue voltage output [V]		0...10		
Min. load resistance [Ω]		2000		
Overload protection		yes		
Measuring/setting range				
Measuring range		0...600 bar	0...8700 psi	0...60 MPa
Accuracy / deviations				
Repeatability [X21]		< 0,1; (with temperature fluctuations < 10 K)		
Characteristics deviation [X21]		< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Hysteresis deviation [X21]		± 1		
Long-term stability [X21]		< ± 0,05; (per 6 months)		
Temperature coefficient zero point [X22]		0,1; (0...80 °C)		
Temperature coefficient span [X22]		0,2; (0...80 °C)		
Response times				
Step response time analogue output [ms]		3		
Operating conditions				
Ambient temperature [°C]		-25...80		
Storage temperature [°C]		-40...100		
Protection		IP 68; IP 69K		
Tests / approvals				
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD		
	EN 61000-4-3 HF radiated	30 V/m		
	EN 61000-4-4 Burst	2 kV		
	EN 61000-4-6 HF conducted	10 V		
	radiation of interference	according to the automotive directive 2004/104/EC		
	CISPR 25			
	immunity	according to the automotive directive 2004/104/EC		
	ISO 11452-2 HF radiated	100 V/m		
Shock resistance	ISO 7637-2 pulse	severity level 4		
	DIN EN 60068-2-27	50 g (11 ms)		
	DIN EN 61373	category 3		
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)		
	DIN EN 61373	category 2		
MTTF [ANN]	478			
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
Railway applications	DIN EN 50155 / IEC 60571	Klasse T3, C1, S1		
Mechanical data				
Weight [g]	232			
Materials	stainless steel (316L/1.4404); FKM; PA; EPDM/X			
Materials (wetted parts)	stainless steel (316L/1.4404); ceramics; FKM			
Min. pressure cycles	100 million			
Process connection	threaded connection G 1/4 internal thread			

PA9060



Pressure transmitter with ceramic measuring cell

PA-600-SBR14-B-DVG/US/V

Restrictor element integrated	yes
-------------------------------	-----

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

