




## Pressure sensor with LED bar display

PB-001PRBU76-HFPKG/US/ IV

Article no longer available - archive entry



## Product characteristics

|                              |                                                    |
|------------------------------|----------------------------------------------------|
| Number of inputs and outputs | Number of digital outputs: 1                       |
| Measuring range [psi]        | 0...10                                             |
| Process connection           | threaded connection 7/16" - 20 UNF internal thread |

## Application

|                              |                             |
|------------------------------|-----------------------------|
| Special feature              | Gold-plated contacts        |
| Application                  | for industrial applications |
| Media                        | liquids and gases           |
| Medium temperature [°C]      | -25...80                    |
| Min. bursting pressure [psi] | 450                         |
| Pressure rating [psi]        | 150                         |
| Type of pressure             | relative pressure           |

## Electrical data

|                                 |                 |
|---------------------------------|-----------------|
| Operating voltage [V]           | 18...30 DC      |
| Current consumption [mA]        | < 50            |
| Min. insulation resistance [MΩ] | 100; (500 V DC) |
| Protection class                | III             |
| Reverse polarity protection     | yes             |
| Power-on delay time [s]         | 0.2             |
| Integrated watchdog             | yes             |



## Pressure sensor with LED bar display

PB-001PRBU76-HFPKG/US/ IV

| Inputs / outputs                                |                           |                                                                     |
|-------------------------------------------------|---------------------------|---------------------------------------------------------------------|
| Number of inputs and outputs                    |                           | Number of digital outputs: 1                                        |
| Outputs                                         |                           |                                                                     |
| Total number of outputs                         |                           | 1                                                                   |
| Output signal                                   |                           | switching signal                                                    |
| Electrical design                               |                           | PNP                                                                 |
| Number of digital outputs                       |                           | 1                                                                   |
| Output function                                 |                           | normally open / normally closed; (parameterisable)                  |
| Max. voltage drop switching output DC           | [V]                       | 2                                                                   |
| Permanent current rating of switching output DC | [mA]                      | 250                                                                 |
| Switching frequency DC                          | [Hz]                      | 10                                                                  |
| Short-circuit protection                        |                           | yes                                                                 |
| Type of short-circuit protection                |                           | pulsed                                                              |
| Overload protection                             |                           | yes                                                                 |
| Measuring/setting range                         |                           |                                                                     |
| Measuring range                                 | [psi]                     | 0...10                                                              |
| Set point SP                                    | [psi]                     | 0.5...10                                                            |
| Reset point rP                                  | [psi]                     | 0.3...9.8                                                           |
| In steps of                                     | [psi]                     | 0.1                                                                 |
| Note on hysteresis                              |                           | adjustable                                                          |
| Accuracy / deviations                           |                           |                                                                     |
| Switch point accuracy                           | [X16]                     | < ± 2,0                                                             |
| Repeatability                                   | [X16]                     | < ± 0,25; (with temperature fluctuations < 10 K)                    |
| Temperature drift per 10 K                      |                           | < ± 0.3                                                             |
| Software / programming                          |                           |                                                                     |
| Adjustment of the switch point                  |                           | programming button                                                  |
| Operating conditions                            |                           |                                                                     |
| Ambient temperature                             | [°C]                      | -25...80                                                            |
| Storage temperature                             | [°C]                      | -40...100                                                           |
| Protection                                      |                           | IP 65                                                               |
| Tests / approvals                               |                           |                                                                     |
| EMC                                             | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD                                                   |
|                                                 | EN 61000-4-3 HF radiated  | 10 V/m                                                              |
|                                                 | EN 61000-4-4 Burst        | 2 kV                                                                |
|                                                 | EN 61000-4-6 HF conducted | 10 V                                                                |
| Shock resistance                                | DIN IEC 68-2-27           | 50 g (11 ms)                                                        |
| Vibration resistance                            | DIN IEC 68-2-6            | 20 g (10...2000 Hz)                                                 |
| Mechanical data                                 |                           |                                                                     |
| Materials                                       |                           | EPDM/X; FKM; NBR; PA; PBT; PC; PTFE; stainless steel (1.4301 / 304) |
| Materials (wetted parts)                        |                           | FKM; ceramics; stainless steel (1.4305 / 303)                       |
| Min. pressure cycles                            |                           | 100 million                                                         |

PB5327



Pressure sensor with LED bar display

PB-001PRBU76-HFPKG/US/ IV

|                    |                                                    |
|--------------------|----------------------------------------------------|
| Process connection | threaded connection 7/16" - 20 UNF internal thread |
|--------------------|----------------------------------------------------|

Displays / operating elements

|         |                  |                                                   |
|---------|------------------|---------------------------------------------------|
| Display | switching status | LED, yellow                                       |
|         | measured values  | 10 x LED, green Resolution 10% of the final value |

Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated

