


PN5122



Pressure sensor with display

PN-100-SBM12-HFPKG/US/.../V

Article no longer available - archive entry



- 1 7-segment LED display
2 programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Measuring range [bar]	0...100
Process connection	threaded connection M12 x 1,5 internal thread ISO 6149

Application

Special feature	Gold-plated contacts
Application	for industrial applications
Media	liquids and gases
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.
Medium temperature [°C]	-25...80
Min. bursting pressure [bar]	650
Pressure rating [bar]	300
Type of pressure	relative pressure

Electrical data

Operating voltage [V]	18...30 DC
Current consumption [mA]	< 60
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	0.2
Integrated watchdog	yes



Pressure sensor with display

PN-100-SBM12-HFPKG/US/.../V

Inputs / outputs											
Number of inputs and outputs		Number of digital outputs: 1									
Outputs											
Total number of outputs		1									
Output signal		switching signal									
Electrical design		PNP									
Number of digital outputs		1									
Output function		normally open / normally closed; (parameterisable)									
Max. voltage drop switching output DC [V]		2									
Permanent current rating of switching output DC [mA]		250									
Short-circuit protection		yes									
Type of short-circuit protection		pulsed									
Overload protection		yes									
Measuring/setting range											
Measuring range [bar]		0...100									
Set point SP [bar]		1...100									
Reset point rP [bar]		0.5...99.5									
In steps of [bar]		0.5									
Accuracy / deviations											
Switch point accuracy [X16]		< ± 1,0									
Repeatability [X16]		< ± 0,25; (with temperature fluctuations < 10 K)									
Temperature drift per 10 K		< ± 0.3									
Response times											
Switching frequency for a given set response time of one output		Response time [ms] (dAP)	3	6	10	17	30	60	125	250	500
		Switching frequency [Hz]	170	80	50	30	16	8	4	2	1
Response time [ms]		at rectangular pressure characteristic; switch point (SPx) = 70 %; reset point (rPx) = 30 %									
Delay time programmable dS, dr [s]		0, 0,2,...10, 11,...50									
Software / programming											
Adjustment of the switch point		programming button									
Parameter setting options		hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping									
Operating conditions											
Ambient temperature [°C]		-25...80									
Storage temperature [°C]		-40...100									
Protection		IP 67									

PN5122



Pressure sensor with display

PN-100-SBM12-HFPKG/US/.../V

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data	
Dimensions [mm]	Ø 34 / L = 91.5
Materials	EPDM/X; FKM; PA; PBT; PC; stainless steel (1.4301 / 304)
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM
Min. pressure cycles	100 million
Process connection	threaded connection M12 x 1,5 internal thread ISO 6149

Displays / operating elements		
Display	switching status	LED, red
	function display	7-segment LED display
	measured values	7-segment LED display

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

