

PN7009




Pressure sensor with display

PN-1-1BRBR14-QFRKG/US/ /

phase-out article

Alternative articles: PN7099
When selecting an alternative article and accessories please note that technical data may differ!



- 1 alphanumeric display 4-digit
- 2 LEDs Display unit / switching status
- 3 programming button



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	-1...1 bar	-1000...1000 mbar
Process connection	threaded connection G 1/4 internal thread	
Application		
Special feature	Gold-plated contacts	
Application	for industrial applications	
Media	liquids and gases	
Medium temperature	[°C]	-25...80
Min. bursting pressure	[mbar]	50000
Pressure rating	[mbar]	20000
Type of pressure	relative pressure	
Electrical data		
Operating voltage	[V]	18...36 DC; (to SELV/PELV)
Current consumption	[mA]	< 35
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class	III	



Pressure sensor with display

PN-1-1BRBR14-QFRKG/US/ /

Reverse polarity protection	yes
Overvoltage protection	yes; (< 40 V)
Power-on delay time [s]	0.3
Integrated watchdog	yes
Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 2
Outputs	
Total number of outputs	2
Output signal	switching signal; IO-Link; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	< 170
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Measuring/setting range	
Measuring range	-1...1 bar -1000...1000 mbar
Set point SP [mbar]	-970...1000
Reset point rP [mbar]	-980...990
In steps of [mbar]	10
Factory setting	SP1 = -500 mbar rP1 = -540 mbar SP2 = 500 mbar rP2 = 460 mbar
Accuracy / deviations	
Switch point accuracy [X21]	< ± 0,5
Repeatability [X21]	< ± 0,1; (with temperature fluctuations < 10 K)
Characteristics deviation [X21]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)
Hysteresis deviation [X21]	< ± 0,25
Long-term stability [X21]	< ± 0,05; (per 6 months)
Temperature coefficient zero point [X22]	0,2; (-20...80 °C)
Temperature coefficient span [X22]	0,2; (-20...80 °C)
Response times	
Delay time programmable dS, dr [s]	0; 0,2...50
Software / programming	
Parameter setting options	hysteresis / window; normally open / normally closed; diagnostic function; switching logic; switch-on/switch-off delay; Damping; Display unit
Interfaces	
Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)



Pressure sensor with display

PN-1-1BRBR14-QFRKG/US/ /

IO-Link revision	1.1				
SDCI standard	IEC 61131-9 CDV				
Profiles	no profile				
SIO mode	yes				
Required master port type	A				
Process data analogue	1				
Process data binary	2				
Min. process cycle time [ms]	2.3				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>314</td></tr> </table>	Type of operation	DeviceID	default	314
Type of operation	DeviceID				
default	314				

Operating conditions		
Ambient temperature [°C]		-20...80
Storage temperature [°C]		-40...100
Protection		IP 65

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF [ANN]		219
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]		261
Materials	stainless steel (304/1.4301); stainless steel (316L/1.4404); PC; PBT; PEI; FKM; PTFE	
Materials (wetted parts)	stainless steel (303/1.4305); ceramics; FKM	
Min. pressure cycles		100 million
Process connection	threaded connection G 1/4 internal thread	
Restrictor element integrated	no (can be retrofitted)	

Displays / operating elements		
Display	Display unit	4 x LED, green
	switching status	2 x LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit

Remarks	
Pack quantity	1 pcs.

PN7009



Pressure sensor with display

PN-1-1BRBR14-QFRKG/US/ /

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



OUT1	switching output IO-Link
OUT2	switching output Diagnostic output