

PP7534




Pressure switch with ceramic measuring cell

PP-010-RBG14-QFRKG/US/ IV

Article no longer available - archive entry

Alternative articles: PP7554

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2		
Measuring range	0...10 bar	0...145 psi	0...1000 kPa
Process connection	threaded connection G 1/4 external thread internal thread:M5		

Application

Special feature	Gold-plated contacts		
Application	for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	-25...90; (on request: -40...90 °C)		
Min. bursting pressure	150 bar	2175 psi	15000 kPa
Pressure rating	50 bar	725 psi	5000 kPa
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	9.6...30 DC		
Current consumption [mA]	< 45		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	0.3		



Pressure switch with ceramic measuring cell

PP-010-RBG14-QFRKG/US/ /V

Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2	
Outputs			
Total number of outputs		2	
Output signal		switching signal	
Electrical design		PNP/NPN	
Number of digital outputs		2	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]		2	
Permanent current rating of switching output DC [mA]		250	
Switching frequency DC [Hz]		< 170	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range		0...10 bar	0...145 psi0...1000 kPa
Set point SP		0.1...9.99 bar	1...145 psi10...999 kPa
Reset point rP		0.05...9.94 bar	1...144 psi5...994 kPa
In steps of		0.01 bar	1 psi1 kPa
Accuracy / deviations			
Switch point accuracy [X21]		< ± 1,5	
Repeatability [X21]		< ± 0,1; (with temperature fluctuations < 10 K)	
Characteristics deviation [X21]		< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)	
Linearity deviation [X21]		< ± 0,5	
Hysteresis deviation [X21]		< ± 0,1	
Long-term stability [X21]		< ± 0,1; (per year)	
Response times			
Response time [ms]		< 3	
Damping process value dAP [s]		0...4	
Software / programming			
Adjustment of the switch point		programming unit / teach function	
Interfaces			
Communication interface		EPS	
Operating conditions			
Ambient temperature [°C]		-40...90	
Storage temperature [°C]		-40...100	
Protection		IP 68; (BFSL = Best Fit Straight Line; LS = limit value setting)	



Pressure switch with ceramic measuring cell

PP-010-RBG14-QFRKG/US/ /V

Tests / approvals		
EMC	radiation of interference	according to the automotive directive 1995/54/EC
	immunity	according to the automotive directive 1995/54/EC annex IX
	HF radiated	150 V/m
	pulse resistance	ISO 7637
	supply	ISO 7637-2 (Pulse 1a, 1b, 2, 3a, 3b, 4, 6, 7)
	signal cables	ISO 7637-3 (Pulse a und b)
	immunity	EN 61000-6-2
	EN 61000-4-2 ESD	8/15 kV
	EN 61000-4-3 HF radiated	100 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 60068-2-27 / DIN IEC 60068-2-29	1000 g
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Materials	stainless steel (1.4301 / 304); FKM; PEI	
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM	
Min. pressure cycles	100 million	
Process connection	threaded connection G 1/4 external thread internal thread:M5	
Restrictor element integrated	no (can be retrofitted)	
Displays / operating elements		
Display	operation	LED, green
	switching status	2 x LED, yellow
Teach function	yes	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		
		

PP7534



Pressure switch with ceramic measuring cell

PP-010-RBG14-QFRKG/US/ /V

Connection

