




Flush pressure sensor with display

PI-100-SEA01-MFRKG/US/ /P

Article no longer available - archive entry

Alternative articles: PI2692

When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
- 2 programming button



EHEDG Certified



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	-1...100 bar	-10...1450 psi	-0.1...10 MPa
Process connection	threaded connection G 1 external thread		

Application

Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	freely rotatable housing 350°		
Media	viscous media and liquids with suspended particles; liquids and gases		
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	650 bar	9425 psi	65 MPa
Pressure rating	200 bar	2900 psi	20 MPa
Type of pressure	relative pressure		



Flush pressure sensor with display

PI-100-SEA01-MFRKG/US/ /P

No dead space	yes
---------------	-----

Electrical data	
Operating voltage [V]	20...30 DC; ("supply class 2" to cULus)
Current consumption [mA]	< 60
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	0.2
Integrated watchdog	yes

Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1

Outputs	
Total number of outputs	2
Output signal	switching signal; analogue signal; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	< 170
Number of analogue outputs	1
Analogue current output [mA]	4...20; (scalable 1:4)
Max. load [Ω]	(U _b - 10 V) / 20 mA
Analogue voltage output [V]	0...10; (scalable 1:4)
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range			
Measuring range	-1...100 bar	-10...1450 psi	-0.1...10 MPa
Set point SP	0...100 bar	0...1450 psi	0...10 MPa
Reset point rP	-0.5...99.5 bar	-10...1440 psi	-0.05...9.95 MPa
Analogue start point	-1...75 bar	-10...1090 psi	-0.1...7.5 MPa
Analogue end point	24...100 bar	350...1450 psi	2.4...10 MPa
In steps of	0.1 bar	10 psi	0.01 MPa

Accuracy / deviations	
Repeatability [X21]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation [X21]	< ± 0,6; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)
Linearity deviation [X21]	< ± 0,5; (Turn down 1:1)
Hysteresis deviation [X21]	< ± 0,1; (Turn down 1:1)
Long-term stability [X21]	< ± 0,1; (Turn down 1:1; per year)



Flush pressure sensor with display

PI-100-SEA01-MFRKG/US/ IP

Temperature coefficient zero point	[X22]	< ± 0,1; (0...80 °C)	
Temperature coefficient span	[X22]	< ± 0,2; (0...80 °C)	
Response times			
Response time	[ms]	< 3	
Damping process value dAP	[s]	0...4	
Damping for the analogue output dAA in steps	[s]	0 - 0,1 - 0,5 - 2	
Max. response time analogue output	[ms]	3	
Software / programming			
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span		
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67	
Tests / approvals			
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	10 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-5 Surge	0,5/1 kV	
	EN 61000-4-6 HF conducted	10 V	
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)	
Mechanical data			
Materials	stainless steel (1.4404 / 316L); PBT; PC; PEI; EPDM/X; FKM		
Materials (wetted parts)	stainless steel (1.4404 / 316L); ceramics; PTFE		
Min. pressure cycles	100 million		
Process connection	threaded connection G 1 external thread		
Displays / operating elements			
Display	switching status	2 x LED, red	
	function display	7-segment LED display	
	measured values	7-segment LED display	
Display unit	bar; psi; MPa		
Remarks			
Remarks	The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.		
Pack quantity	1 pcs.		



Flush pressure sensor with display

PI-100-SEA01-MFRKG/US/ /P

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1
OUT2

switching output
switching output
analogue output