




Flush pressure sensor with display

PI-001BRES30-MFRKG/US/ /P

Article no longer available - archive entry

Alternative articles: PI2097 or PI1097

When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
- 2 programming button
- 3 Aseptoflex sealing edge
- 4 Aseptoflex thread
- 5 diaphragm : PTFE



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	-50...1000 mbar	-0.7...14.5 psi	-5...100 kPa
Process connection	threaded connection Aseptoflex external thread Aseptoflex		

Application

Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	freely rotatable housing 350°		
Media	liquid and viscous media		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	30000 mbar	450 psi	3000 kPa
Pressure rating	10000 mbar	145 psi	1000 kPa
Type of pressure	relative pressure		
No dead space	yes		



Flush pressure sensor with display

PI-001BRES30-MFRKG/US/ /P

Electrical data			
Operating voltage	[V]	20...30 DC; ("supply class 2" to cULus)	
Current consumption	[mA]	< 60	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	0.2	
Integrated watchdog		yes	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1	
Outputs			
Total number of outputs		2	
Output signal		switching signal; analogue signal; (configurable)	
Electrical design		PNP/NPN	
Number of digital outputs		2	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	< 170	
Number of analogue outputs		1	
Analogue current output	[mA]	4...20; (scalable 1:4)	
Max. load	[Ω]	(Ub - 10 V) / 20 mA	
Analogue voltage output	[V]	0...10; (scalable 1:4)	
Min. load resistance	[Ω]	2000	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range		-50...1000 mbar	-0.7...14.5 psi -5...100 kPa
Set point SP		-45...999 mbar	-0.7...14.5 psi -4.5...99.9 kPa
Reset point rP		-50...994 mbar	-0.7...14.4 psi -5...99.4 kPa
Analogue start point		-50...749 mbar	-0.7...10.9 psi -5...74.9 kPa
Analogue end point		200...999 mbar	2.9...14.5 psi 20...99.9 kPa
In steps of		1 mbar	0.1 psi 0.1 kPa
Accuracy / deviations			
Repeatability	[X21]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	[X21]	< ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)	
Linearity deviation	[X21]	< ± 0,5; (Turn down 1:1)	
Hysteresis deviation	[X21]	< ± 0,1; (Turn down 1:1)	
Long-term stability	[X21]	< ± 0,1; (Turn down 1:1; per year)	
Temperature coefficient zero point	[X22]	< ± 0,15; (0...80 °C)	



Flush pressure sensor with display

PI-001BRES30-MFRKG/US/ /P



Temperature coefficient span	[X22]	< ± 0,4; (0...80 °C)	
Response times			
Response time	[ms]	< 3	
Damping process value dAP	[s]	0...4	
Damping for the analogue output dAA in steps	[s]	0 - 0,1 - 0,5 - 2	
Max. response time analogue output	[ms]	3	
Software / programming			
Parameter setting options		hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67	
Tests / approvals			
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	10 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)	
Mechanical data			
Materials		stainless steel (1.4404 / 316L); PBT; PC; PA; EPDM/X; FKM	
Materials (wetted parts)		stainless steel (1.4435 / 316L); PTFE on ceramic substrate; PTFE	
Min. pressure cycles		100 million	
Process connection		threaded connection Aseptoflex external thread Aseptoflex	
Displays / operating elements			
Display	switching status	2 x LED, red	
	function display	7-segment LED display	
	measured values	7-segment LED display	
Display unit		mbar; psi; kPa	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Connector: 1 x M12; coding: A; Contacts: gold-plated			
			



Flush pressure sensor with display

PI-001BRES30-MFRKG/US/ /P

Connection



OUT1
OUT2

switching output
switching output
analogue output