


PK5723



Pressure switch with intuitive switch point setting

PK-025-SFR14-PSPKG/US/ IW



1 Tightening torque 25 Nm



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 1	
Measuring range	0...25 bar	0...2.5 MPa
Process connection	threaded connection R 1/4 external thread internal thread:M5	
Application		
Application	for industrial applications	
Media	liquids and gases	
Medium temperature [°C]	-25...80	
Min. bursting pressure	500 bar	50 MPa
Pressure rating	60 bar	6 Mpa
Type of pressure	relative pressure	
Electrical data		
Operating voltage [V]	9.6...32 DC; (to SELV/PELV)	
Current consumption [mA]	< 25	
Min. insulation resistance [MΩ]	100; (500 V DC)	
Protection class	III	
Reverse polarity protection	yes	
Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 1	
Outputs		
Total number of outputs	1	
Output signal	switching signal	
Electrical design	PNP	
Number of digital outputs	1	
Output function	normally open	



Pressure switch with intuitive switch point setting

PK-025-SFR14-PSPKG/US/ IW

Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	500
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Measuring/setting range		
Measuring range	0...25 bar	0...2.5 MPa
Set point SP	0.75...25 bar	0.075...2.5 MPa
Hysteresis	0.5 bar	0.05 MPa

Accuracy / deviations		
Switch point accuracy	[X16]	$< \pm 2,5$; (Setting accuracy)
Repeatability	[X16]	$< \pm 0,5$; (with temperature fluctuations < 10 K)
Characteristics deviation	[X16]	$< \pm 1,5$ (BFSL) / $< \pm 2,5$ (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)
Temperature drift per 10 K		$< \pm 0.5$

Software / programming	
Adjustment of the switch point	setting ring

Operating conditions	
Ambient temperature	[°C] -25...80
Storage temperature	[°C] -40...100
Protection	IP 67

Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	771
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	96
Materials	PBT; PC; FKM; stainless steel (1.4404 / 316L)	
Materials (wetted parts)	stainless steel (1.4404 / 316L)	
Min. pressure cycles	50 million	
Tightening torque	[Nm]	25; (recommended tightening torque; depends on lubrication, seal and pressure rating)
Process connection	threaded connection R 1/4 external thread internal thread:M5	
Restrictor element integrated	no (can be retrofitted)	

Displays / operating elements		
Display	operation	LED, green
	switching status	LED, yellow

Remarks	
Pack quantity	1 pcs.



Pressure switch with intuitive switch point setting


PK-025-SFR14-PSPKG/US/ IW

Electrical connection

Connector: 1 x M12; coding: A



Connection



OUT switching output
 colours to DIN EN 60947-5-2
 Core colours :

BK = black
BN = brown
BU = blue