


PX9020



Pressure transmitter with ceramic measuring cell

PA-400-SBR14-B-DVG/US/ IV



Product characteristics	
Number of inputs and outputs	Number of analogue outputs: 1
Measuring range [bar]	0...400
Process connection	threaded connection G 1/4 internal thread
Application	
Special feature	Gold-plated contacts
Application	for industrial applications
Media	liquids and gases
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.
Medium temperature [°C]	-25...90; (on request: -40...90 °C)
Min. bursting pressure [bar]	1000
Pressure rating [bar]	600
Type of pressure	relative pressure
Electrical data	
Operating voltage [V]	10...30 DC
Current consumption [mA]	< 18
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Inputs / outputs	
Number of inputs and outputs	Number of analogue outputs: 1
Outputs	
Total number of outputs	1
Output signal	analogue signal

PX9020



Pressure transmitter with ceramic measuring cell

PA-400-SBR14-B-DVG/US/ IV

Number of analogue outputs		1
Analogue voltage output	[V]	0.5...4.5
Min. load resistance	[Ω]	2000
Overload protection		yes
Measuring/setting range		
Measuring range	[bar]	0...400
Accuracy / deviations		
Repeatability	[X21]	< 0,1; (with temperature fluctuations < 10 K)
Characteristics deviation	[X21]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)
Long-term stability	[X21]	< ± 0,05; (per 6 months)
Temperature coefficient zero point	[X22]	0,4; (0...80 °C)
Temperature coefficient span	[X22]	0,4; (0...80 °C)
Response times		
Step response time analogue output	[ms]	3
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 68; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	30 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	550
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight	[g]	221.5
Materials		stainless steel (1.4404 / 316L); FKM; PA; EPDM/X
Materials (wetted parts)		stainless steel (1.4305 / 303); ceramics; FKM
Min. pressure cycles		100 million
Process connection		threaded connection G 1/4 internal thread
Restrictor element integrated		yes
Remarks		
Pack quantity		1 pcs.

PX9020



Pressure transmitter with ceramic measuring cell

PA-400-SBR14-B-DVG/US/ IV

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

