


PX9112



Pressure transmitter with ceramic measuring cell

PA-100PSBN14-B-DVG/US/ IV



Product characteristics	
Number of inputs and outputs	Number of analogue outputs: 1
Measuring range [psi]	0...1000
Process connection	threaded connection 1/4" NPT external thread internal thread:M5
Application	
Special feature	Gold-plated contacts
Application	for industrial applications
Media	liquids and gases
Conditionally suitable for	use in gases at pressures > 25 bar only on request
Medium temperature [°C]	-25...90
Min. bursting pressure [psi]	9400
Pressure rating [psi]	4350
Type of pressure	relative pressure
Electrical data	
Operating voltage [V]	16...32 DC
Current consumption [mA]	< 18
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Inputs / outputs	
Number of inputs and outputs	Number of analogue outputs: 1
Outputs	
Total number of outputs	1
Output signal	analogue signal



Pressure transmitter with ceramic measuring cell

PA-100PSBN14-B-DVG/US/ IV

Number of analogue outputs		1
Analogue voltage output	[V]	0...10
Min. load resistance	[Ω]	2000
Overload protection		yes
Measuring/setting range		
Measuring range	[psi]	0...1000
Accuracy / deviations		
Repeatability	[X21]	< 0,15; (with temperature fluctuations < 10 K)
Characteristics deviation	[X21]	< ± 0,35 (BFSL) / < ± 0,75 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)
Long-term stability	[X21]	< ± 0,05; (per 6 months)
Temperature coefficient zero point	[X22]	0,2; (0...80 °C)
Temperature coefficient span	[X22]	0,3; (0...80 °C)
Response times		
Step response time analogue output	[ms]	3
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 68; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	30 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	radiation of interference	according to the automotive directive 2004/104/EC / CISPR 25
	immunity	according to the automotive directive 2004/104/EC / ISO 11452-2
	HF radiated	100 V/m
	pulse resistance	ISO 7637-2 / severity level 3
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	550
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight	[g]	213
Materials	stainless steel (1.4404 / 316L); FKM; PA; EPDM/X	
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM	
Min. pressure cycles	100 million	
Process connection	threaded connection 1/4" NPT external thread internal thread:M5	
Restrictor element integrated	no (can be retrofitted)	
Remarks		
Pack quantity	1 pcs.	

PX9112



Pressure transmitter with ceramic measuring cell

PA-100PSBN14-B-DVG/US/ /V

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

