




Absolute multiturn encoder with solid shaft

RM-4096-S24/N1B

Article no longer available - archive entry



- 1 reference mark
- 2 M4 Depth 5 mm



Product characteristics

Resolution	4096 resolution; 4096 steps; 4096 revolutions; 24 bit
Communication interface	SSI data interface
Shaft design	solid shaft
Shaft diameter [mm]	10

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 200

Outputs

Code	Gray code; (increasing code values when turned clockwise (seen on the shaft))
Code signal	Clock input; TTL-compatible signals; clock and clock (inv.) from drivers to RS 485; data output; synchronous serial; TTL-compatible signals, data, and data (inv.); incremental signals; 2 sinusoidal incremental signals (A and B) ; phase shifted by 90°; 1 Vss 512 signal periods per revolution

Measuring/setting range

Resolution	4096 resolution; 4096 steps; 4096 revolutions; 24 bit
------------	---

Interfaces

Communication interface	SSI data interface
-------------------------	--------------------

Operating conditions

Ambient temperature [°C]	-40...85
--------------------------	----------

RM6004



Absolute multiturn encoder with solid shaft

RM-4096-S24/N1B

Max. relative air humidity [%]	75; (briefly: 95 %)
Protection	IP 64

Tests / approvals

Shock resistance	100 g (6 ms)
Vibration resistance	30 g (55...2000 Hz)

Mechanical data

Weight [g]	490
Dimensions [mm]	Ø 58 / L = 66.7
Materials	aluminium
Max. revolution, mechanical [U/min]	12000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	10
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	10
Max. shaft load radial (at the shaft end) [N]	20

Remarks

Remarks	Wires/pins not connected (n.c.) must not be used.
---------	---

Electrical connection

Cable: 1 m, PUR; Maximum cable length: 100 m; radial, can also be used axially

black	n.c.
red	n.c.
green	n.c.
brown	n.c.
brown/green	10...30V (Up)
lilac	clock
yellow	clock inverted
screen	housing
white/green	0V (Un)
blue / black	B+
red/black	B-
grey	data
green / black	A+
yellow / black	A-
pink	data inverted

Diagrams and graphs

Pulse diagram

