




Pressure sensor with display

PN-010-RDR14-KFPKG/US/ IV

Article no longer available - archive entry



- 1 7-segment LED display
- 2 programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1
Measuring range [bar]	0...10
Process connection	threaded connection G 1/4 internal thread

Application

Special feature	Gold-plated contacts
Application	for industrial applications
Media	liquids and gases
Medium temperature [°C]	-25...80
Min. bursting pressure [bar]	150
Pressure rating [bar]	50
Type of pressure	relative pressure

Electrical data

Operating voltage [V]	20...30 DC
Current consumption [mA]	< 60
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	0.2
Integrated watchdog	yes



Pressure sensor with display

PN-010-RDR14-KFPKG/US/ IV

Inputs / outputs												
Number of inputs and outputs			Number of digital outputs: 1; Number of analogue outputs: 1									
Outputs												
Total number of outputs			2									
Output signal			switching signal; analogue signal; (configurable)									
Electrical design			PNP									
Number of digital outputs			1									
Max. voltage drop switching output DC [V]			2									
Permanent current rating of switching output DC [mA]			250									
Number of analogue outputs			1									
Analogue current output [mA]			4...20									
Max. load [Ω]			500									
Short-circuit protection			yes									
Type of short-circuit protection			pulsed									
Overload protection			yes									
Measuring/setting range												
Measuring range [bar]			0...10									
Set point SP [bar]			0.1...10									
Reset point rP [bar]			0.05...9.95									
In steps of [bar]			0.05									
Accuracy / deviations												
Switch point accuracy [X16]			< ± 1,5									
Repeatability [X16]			< ± 0,25; (with temperature fluctuations < 10 K)									
Characteristics deviation [X16]			< ± 1,0									
Temperature drift per 10 K			< ± 0.3									
Response times												
Switching frequency for a given set response time of one output			Response time (dAP) [ms]	3	6	10	17	30	60	125	250	500
			Switching frequency [Hz]	170	80	50	30	16	8	4	2	1
Response time [ms]			at rectangular pressure characteristic; switch point (SPx) = 70 %; reset point (rPx) = 30 %									
Delay time programmable dS, dr [s]			0, 0,2,...10, 11,...50									
Max. response time analogue output [ms]			3									
Software / programming												
Adjustment of the switch point			programming button									
Parameter setting options			hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping									
Operating conditions												
Ambient temperature [°C]			-25...80									
Storage temperature [°C]			-40...100									

PN3054



Pressure sensor with display

PN-010-RDR14-KFPKG/US/ IV

Protection	IP 65
------------	-------

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data

Materials	EPDM/X; FKM; PA; PBT; PC; PTFE; stainless steel (1.4404 / 316L); stainless steel (1.4539 / 904L)
Materials (wetted parts)	FKM; ceramics; stainless steel (1.4539 / 904L)
Min. pressure cycles	100 million
Process connection	threaded connection G 1/4 internal thread

Displays / operating elements

Display	switching status	LED, red
	function display	7-segment LED display
	measured values	7-segment LED display

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

