


RMV300



Absolute multiturn encoder with solid shaft

MULTITURN ENCODER STANDARD LINE



- 1 M4 x 0.7 Depth 6 mm
2 M3 x 0.5 Depth 6 mm



Product characteristics

Resolution	65536 steps; 32768 revolutions; 31 bit
Communication interface	IO-Link
Shaft design	solid shaft
Shaft diameter [mm]	10

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage [V]	18...30 DC; (; to PELV)
Rated insulation voltage [V]	30
Current consumption [mA]	< 75
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	1000
Max. revolution electrical [U/min]	12000

Outputs

Short-circuit protection	yes
--------------------------	-----

Measuring/setting range

Resolution	65536 steps; 32768 revolutions; 31 bit
------------	--

Accuracy / deviations

Accuracy [°]	0.1
--------------	-----



Absolute multiturn encoder with solid shaft

MULTITURN ENCODER STANDARD LINE

Software / programming		
Parameter setting options	preset; zero point; direction of rotation; rotational speed	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Function class	Designation
	0x4000	Identification and Diagnosis
	0x8001	Switching Signal Channel
	0x800B	Measurement Data Channel (high resolution)
SIO mode	no	
Required master port type	A	
Min. process cycle time [ms]	2.3	
IO-Link process data (cyclical)	function	bit length
	process value	96
	device status	4
	binary switching information	5
IO-Link functions (acyclical)	application specific tag; operating hours counter; internal temperature; switching cycles counter	
Supported DeviceIDs	Type of operation	DeviceID
	default	1064
Note	For further information please see the IODD PDF file under "Downloads"	
Operating conditions		
Ambient temperature [°C]	-40...85	
Storage temperature [°C]	-40...85	
Max. relative air humidity [%]	98; (condensation not permissible)	
Protection	IP 65; (on the housing: IP 67; on the shaft: IP 65)	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD
	DIN EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-6 HF conducted	10 V
Vibration resistance	DIN EN 60068-2-6	10 g / 10...1000 Hz half-sine
Shock resistance	DIN EN 60068-2-27	100 g 6 ms
Continuous shock resistance	DIN EN 60068-2-29	10 g / 16 ms half-sine
Vibration resistance		30 g (10...1000 Hz)
MTTF [ANN]	283	
UL approval	подача напруги	Class 2
Mechanical data		
Weight [g]	370.9	
Dimensions [mm]	Ø 58 / L = 79	
Materials	flange: aluminium; housing: stainless steel (1.4521 / 444)	
Max. starting torque [Nm]	1	
Reference temperature torque [°C]	20	

RMV300




Absolute multiturn encoder with solid shaft

MULTITURN ENCODER STANDARD LINE

Shaft design	solid shaft	
Shaft diameter [mm]	10	
Shaft material	stainless steel	
Max. shaft load axial (at the shaft end) [N]	40	
Max. shaft load radial (at the shaft end) [N]	110	
Fixing flange	clamping flange	

Electrical connection - plug

Connector: 1 x M12, radial, can also be used axially; coding: A; Moulded body: stainless steel (316 / 1.4401)



1	UB
2	SSC1.2 / IN
3	GND
4	IO-Link
5	n. c.