

RV1070



Incremental encoder with solid shaft

RV-2500-I05/SAE

Article no longer available - archive entry



- | | |
|---|----------------|
| 1 | reference mark |
| 2 | M3 Depth 5 mm |



Product characteristics

Resolution	2500 resolution
Shaft design	solid shaft
Shaft diameter [mm]	10

Electrical data

Operating voltage tolerance	[%]	10
Operating voltage	[V]	5 DC
Current consumption	[mA]	150

Outputs

Electrical design	TTL
Max. current load per output [mA]	20
Switching frequency [kHz]	300
Phase difference A and B [°]	90

Measuring/setting range

Resolution	2500 resolution
------------	-----------------

Operating conditions

Ambient temperature	[°C]	-20...70
Storage temperature	[°C]	-30...100
Protection		IP 66

Tests / approvals

Shock resistance	100 g (6 ms)
------------------	--------------

RV1070



Incremental encoder with solid shaft

RV-2500-I05/SAE

Vibration resistance	10 g (55...2000 Hz)
----------------------	---------------------


Mechanical data

Dimensions	[mm]	Ø 58 / L = 46
Materials		aluminium
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20

Electrical connection


Cable: 10 m, PUR; axial

Connector: 1 x Bajonett (ifm 1000.2)



pin 1	A
pin 2	A inverted
pin 3	B
pin 4	B inverted
pin 5	+5V sensor
pin 6	0 index
pin 7	0 index inverted
pin 9	+5V (Up)
pin 10	0V sensor
pin 11	housing
pin 12	0V (Un)

Diagrams and graphs

Pulse diagram	 direction of rotation clockwise (looking at the shaft)
---------------	--