


PQ3809



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPKG/AS/



- 1 main pressure connection G 1/8 Tightening torque < 8 Nm insertion depth < 7.5 mm
- 2 auxiliary pressure connection M 5 Tightening torque < 2.5 Nm insertion depth < 7.5 mm
- 3 Tightening torque < 0.5 Nm
- 4 LEDs Display unit / switching status
- 5 alphanumeric display 4-digit
- 6 programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1				
Measuring range	-1...1 bar	-1000...1000 mbar	-14.6...14.6 psi	-29.4...29.4 inHg	-100...100 kPa
Process connection	threaded connection G 1/8 internal thread internal thread:M5				

Application

Special feature	Gold-plated contacts			
Application	for industrial applications			
Conditionally suitable for	other media on request			
Medium temperature [°C]	0...60			
Min. bursting pressure	30 bar	435 psi	886 inHg	3000 kPa
Note on min. burst pressure	max. overpressure on second pressure connection: 12 bar / 1200 kPa / 174 PSI / 354,4 inHg / 1,2 MPa			
Pressure rating	20 bar	290 psi	591 inHg	2000 kPa
Vacuum resistance [mbar]	-1000			



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPKG/AS/

Type of pressure	relative pressure; differential pressure; vacuum					
Electrical data						
Operating voltage	[V]	18...32 DC; (to SELV/PELV)				
Current consumption	[mA]	< 50				
Min. insulation resistance	[MΩ]	100; (500 V DC)				
Protection class		III				
Reverse polarity protection		yes				
Overvoltage protection		yes; (< 40 V)				
Power-on delay time	[s]	0.5				
Integrated watchdog		yes				
Inputs / outputs						
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1				
Outputs						
Total number of outputs		2				
Output signal		switching signal; analogue signal; IO-Link; (configurable)				
Electrical design		PNP				
Number of digital outputs		1				
Output function		normally open / normally closed; (parameterisable)				
Max. voltage drop switching output DC	[V]	2				
Permanent current rating of switching output DC	[mA]	100				
Switching frequency DC	[Hz]	< 100				
Number of analogue outputs		1				
Analogue current output	[mA]	4...20				
Max. load	[Ω]	500				
Short-circuit protection		yes				
Type of short-circuit protection		pulsed				
Measuring/setting range						
Measuring range		-1...1 bar	-1000...1000 mbar	-14.6...14.6 psi	-29.4...29.4 inHg	-100...100 kPa
Set point SP		-0.98...1 bar	-14.2...14.6 psi	-28.8...29.4 inHg	-98...100 kPa	
Reset point rP		-0.99...0.99 bar	-14.4...14.4 psi	-29.1...29.1 inHg	-99...99 kPa	
In steps of		0.01 bar	0.2 psi	0.3 inHg	1 kPa	
Accuracy / deviations						
Switch point accuracy	[X21]	< ± 0,5				
Repeatability	[X21]	< ± 0,1; (with temperature fluctuations < 10 K)				
Characteristics deviation	[X21]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)				
Hysteresis deviation	[X21]	< ± 0,25				
Long-term stability	[X21]	< ± 0,05; (per 6 months)				
Temperature coefficient zero point	[X22]	0,2; (0...60 °C)				
Temperature coefficient span	[X22]	0,2; (0...60 °C)				



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPG/AS/

Response times		
Response time	[ms]	< 6
Delay time programmable dS, dr	[s]	0; 0,002...5
Step response time analogue output	[ms]	6
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; analogue output; IO-Link; switching logic; switch-on/switch-off delay; Damping; Display unit	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 FDIS	
Profiles	Smart Sensor: Process Data Variable; Device Identification	
SIO mode	yes	
Required master port type	A	
Process data analogue	1	
Process data binary	2	
Min. process cycle time	[ms]	2.3
Supported DeviceIDs	Type of operation	DeviceID
	default	366
Operating conditions		
Ambient temperature	[°C]	0...70
Storage temperature	[°C]	-25...85
Protection	IP 65	
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[ANN]	437
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight	[g]	87
Materials	PBT; FKM; polyester	
Materials (wetted parts)	brass; FKM; silicon (coated); PBT	
Min. pressure cycles	50 million	
Process connection	threaded connection G 1/8 internal thread internal thread:M5	
Displays / operating elements		
Display	Display unit	4 x LED, green
	switching status	1 x LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit
Display unit	bar; kPa; psi; inHg	

PQ3809



Pressure sensor for pneumatics

PQ-1-1-KHR18-KFPKG/AS/

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M8; coding: A; Contacts: gold-plated



Connection



OUT1	switching output IO-Link
OUT2	analogue output