

SA1000




Flow sensor

SAM16BBD100G/W/US

Article no longer available - archive entry

Alternative articles: SA5000

When selecting an alternative article and accessories please note that technical data may differ!



- 1 O-ring
- 2 compression washer



Product characteristics

Process connection M16 x 1,5

Application

Design for pipes DN 40...DN 100

Media water

Note on media
Clean water without contamination and additives.
Dirt/build-up on the sensor tip affects the measurement accuracy.
Check the sensor tip for build-up from time to time.
If necessary, clean with a soft cloth and a vinegar cleansing agent.

Medium temperature [°C] 0...80

Pressure rating [bar] 30

Electrical data

Operating voltage [V] 20...28 DC; (to SELV/PELV)

Current consumption [mA] < 80

Reverse polarity protection yes

Power-on delay time [s] 15

Outputs

Output signal analogue signal

SA1000



Flow sensor

SAM16BBD100G/W/US

| | | |
|--------------------------|------|----------------------|
| Analogue current output | [mA] | 4...20; (linearised) |
| Max. load | [Ω] | 500 |
| Analogue voltage output | [V] | ; (linearised) |
| Short-circuit protection | | no |
| Overload protection | | yes |

Measuring/setting range

| | | |
|------------|--------|---------|
| Flow range | [cm/s] | 3...150 |
|------------|--------|---------|

Accuracy / deviations

| | | |
|-----------------------|---------|-----------------------------------|
| Note on repeatability | | 7 (v < 150 cm/s), 3 (v < 50 cm/s) |
| Temperature gradient | [K/min] | 200 |
| Measuring error | [X16] | max. ± 10 |

Response times

| | | |
|---------------|-----|----------------|
| Response time | [s] | 5; (10%...90%) |
|---------------|-----|----------------|

Operating conditions

| | | |
|---------------------|------|----------|
| Ambient temperature | [°C] | -20...60 |
| Protection | | IP 67 |

Mechanical data

| | | |
|--------------------------|------|--|
| Weight | [g] | 268.8 |
| Dimensions | [mm] | M16 x 1.5 |
| Thread designation | | M16 x 1.5 |
| Materials | | PBT-GF20 |
| Materials (wetted parts) | | stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti); O-ring: NBR 70 Shore A |
| Process connection | | M16 x 1,5 |

Displays / operating elements

| | | |
|---------|----------|---|
| Display | function | 10 x LED, green Resolution 10% of the final value |
|---------|----------|---|

Remarks

| | | |
|---------------|--|--------|
| Pack quantity | | 1 pcs. |
|---------------|--|--------|

Electrical connection

Connector: 1 x M12; coding: A




SA1000



Flow sensor

SAM16BBD100G/W/US

Connection



| | |
|------|----------------|
| BN = | Core colours : |
| BU = | brown |
| BK = | blue |
| WH = | black |
| | white |