



Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 5M PUR CABLE



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1				
Measuring range	0...0.25 bar	0...250 mbar	0...3.63 psi	0...100.4 inH ₂ O	0...25 kPa

Application

Design	with capillary tube for pressure compensation		
Application	for industrial applications		
Media	Liquids		
Medium temperature [°C]	-10...50		
Min. bursting pressure	2.4 bar	35 psi	240 kPa
Pressure rating	2 bar	29 psi	200 kPa
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	10...30 DC
Protection class	III
Reverse polarity protection	yes
Measuring principle	hydrostatic

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	700; (U _b = 24 V; (U _b - 10 V) / 20 mA)
Short-circuit protection	yes

Measuring/setting range

Measuring range	0...0.25 bar	0...250 mbar	0...3.63 psi	0...100.4 inH ₂ O	0...25 kPa
-----------------	--------------	--------------	--------------	------------------------------	------------

Accuracy / deviations


Repeatability [X21]	< 0,1; (with temperature fluctuations < 10 K)
Characteristics deviation [X21]	< 0,5 (BFSL) / 1; (incl. linearity, zero and span error (limit value setting))
Linearity deviation [X21]	< 0,2 (BFSL)
Long-term stability [X21]	< 0,2; (per year)
Temperature coefficient zero point [X22]	< ± 0,2; (0...50 °C)
Temperature coefficient span [X22]	< ± 0,2; (0...50 °C)



Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 5M PUR CABLE

Operating conditions		
Ambient temperature	[°C]	-10...50
Storage temperature	[°C]	-30...80
Protection		IP 68
Tests / approvals		
MTTF	[ANN]	403
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight	[g]	553.6
Materials		stainless steel (1.4571/316Ti); PA
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 5 m, PUR, Ø 7.5 mm; Core insulation:, PVC		
Connection		



Core colours :
 BN = brown
 GY = grey
 WH = white